

**M-D-STRIPAX LWL****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

- With 1 mm diameter inner conductor
- Stripping length adjustable via end stop
- Automatic opening of clamping jaws after stripping

**General ordering data**

Version	Tools, Stripping and cutting tool
Order No.	<a href="#">9003750000</a>
Type	M-D-STRIPAX LWL
GTIN (EAN)	4008 190068042
Qty.	1 pc(s).

Creation date February 28, 2023 6:44:12 PM CET

Catalogue status 18.02.2023 / We reserve the right to make technical changes.

## M-D-STRIPAX LWL

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Dimensions and weights

Depth	16 mm	Depth (inches)	0.63 inch
Height	135 mm	Height (inches)	5.315 inch
Width	82 mm	Width (inches)	3.228 inch
Net weight	96.73 g		

### Technical data

Description of article	Stripping tool for fibre-optic cables
------------------------	---------------------------------------

### Stripping tools

Cable type	POF conductor with an inner conductor of 1 mm	Colour	grey
Max. conductor diameter	1 mm	Stripping length, max.	7.5 mm

### Classifications

ETIM 6.0	EC002109	ETIM 7.0	EC002109
ETIM 8.0	EC002109	ECLASS 9.0	21-04-37-06
ECLASS 9.1	21-04-37-06	ECLASS 10.0	21-04-37-06
ECLASS 11.0	21-04-37-06	ECLASS 12.0	21-04-37-06

### Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	cf06c250-ed1e-4a45-9c1b-c5c8cbf13bf0

### Downloads

Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	