

**H6,0/10****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



- For conductors from 0.25 to 6,0 mm<sup>2</sup> (AWG 24 - 10)  
tin-plated copper  
dimensional tolerances to DIN 46228 part 1
- supplied loose in polybag

**General ordering data**

Version	Wire-end ferrule, Standard, 10 mm, 10 mm, No
Order No.	<a href="#">9004120000</a>
Type	H6,0/10
GTIN (EAN)	4008190104795
Qty.	500 pc(s).
Packaging	loose

Creation date February 17, 2023 11:22:38 AM CET

Catalogue status 03.02.2023 / We reserve the right to make technical changes.

**H6,0/10**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Dimensions and weights

Net weight 0.17 g

### Technical data

Description of article	Wire end ferrule without plastic collar	Version	Standard
------------------------	---	---------	----------

### Wire-end ferrules

Collar diameter (D2)	4.7 mm	Conductor cross-section	6 mm <sup>2</sup>
Contact surface diameter (D1)	3.5 mm	Contact surface length (L2)	10 mm
L1 in mm	10 mm	Stripping length	10 mm
Wire connection cross section AWG, max.	AWG 10		

### Classifications

ETIM 6.0	EC000005	ETIM 7.0	EC000005
ETIM 8.0	EC000005	ECLASS 9.0	27-40-02-01
ECLASS 9.1	27-40-02-01	ECLASS 10.0	27-40-02-01
ECLASS 11.0	27-40-02-01	ECLASS 12.0	27-40-02-01

### Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E499744

### Downloads

Engineering Data	<a href="#">CAD data – STEP</a>
Engineering Data	<a href="#">WSCAD, Zuken E3.S</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	

**Data sheet**

**H6,0/10**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

