

**H50,0/32****Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com



For conductors from 10.0 to 185.0 mm<sup>2</sup> (AWG 7 - 350 MCM)

tin-plated copper

dimensional tolerances to DIN 46228 part 1

- supplied loose in poly-bag

**General ordering data**

|            |  |
|------------|--|
| Version    | Wire-end ferrule, Standard, 32 mm, 32 mm, No |
| Order No.  | <a href="#">9004220000</a>                   |
| Type       | H50,0/32                                     |
| GTIN (EAN) | 4008190059606                                |
| Qty.       | 100 pc(s).                                   |
| Packaging  | loose  |

**H50,0/32**

Weidmüller Interfaces GmbH &amp; Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

**Technical data****Dimensions and weights**

Net weight 2.88 g

**Technical data**

| Description of article | Wire end ferrule without plastic collar | Version | Standard |
|------------------------|---|---------|----------|
|------------------------|---|---------|----------|

**Wire-end ferrules**

|   |         |                             |                    |
|---|---------|-----------------------------|--------------------|
| Collar diameter (D2)                    | 13 mm   | Conductor cross-section     | 50 mm <sup>2</sup> |
| Contact surface diameter (D1)           | 10.3 mm | Contact surface length (L2) | 32 mm              |
| L1 in mm                                | 32 mm   | Stripping length            | 32 mm              |
| Wire connection cross section AWG, max. | AWG 1   |                             |                    |

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC000005    | ETIM 7.0    | EC000005    |
| ETIM 8.0    | EC000005    | ECLASS 9.0  | 27-40-02-01 |
| ECLASS 9.1  | 27-40-02-01 | ECLASS 10.0 | 27-40-02-01 |
| ECLASS 11.0 | 27-40-02-01 | ECLASS 12.0 | 27-40-02-01 |

**Approvals**

Approvals



|                         |            |
|-------------------------|------------|
| ROHS                    | Conform    |
| UL File Number Search   | UL Website |
| Certificate no. (cULus) | E499744    |

**Downloads**

|                  |  |
|------------------|--|
| Engineering Data | <a href="#">CAD data – STEP</a>          |
| Engineering Data | <a href="#">WSCAD, Zuken E3.S</a>        |
| Catalogues       | <a href="#">Catalogues in PDF-format</a> |
| Brochures        |  |

**Data sheet**

**H50,0/32**

**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

[info@weidmueller.com](mailto:info@weidmueller.com)

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

