

## H0,5/14S W

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



- supplied loose in poly-bag
- Weidmüller colour code
- DIN colour code
- other colour code

### General ordering data

Version	Wire-end ferrule, Standard, 10 mm, 8 mm, white
Order No.	<a href="#">9004590000</a>
Type	H0,5/14S W
GTIN (EAN)	4008 190862060
Qty.	500 pc(s).
Packaging	loose

Creation date February 28, 2023 1:35:51 AM CET

Catalogue status 18.02.2023 / We reserve the right to make technical changes.

## H0,5/14S W

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Net weight 0.076 g

## Technical data

Description of article	Wire end ferrule with plastic collar, special size, white	Version	Standard

## Wire-end ferrules

Collar diameter (D2)	2.9 mm	Colour code	Weidmüller
Conductor cross-section	0.5 mm <sup>2</sup>	Contact surface diameter (D1)	1 mm
Contact surface length (L2)	8 mm	L1 in mm	14 mm
Metal sleeve thickness (S1)	0.15 mm	Plastic collar thickness (S2)	0.25 mm
Stripping length	10 mm	Wire connection cross section AWG, max.	AWG 20

## Classifications

ETIM 6.0	EC000005	ETIM 7.0	EC000005
ETIM 8.0	EC000005	ECLASS 9.0	27-40-02-01
ECLASS 9.1	27-40-02-01	ECLASS 10.0	27-40-02-01
ECLASS 11.0	27-40-02-01	ECLASS 12.0	27-40-02-01

## Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E499744

## Downloads

Engineering Data	<a href="#">CAD data – STEP</a>
Engineering Data	<a href="#">WSCAD</a>
User Documentation	<a href="#">Technical information - EN</a> <a href="#">Technical information - DE</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	

**Data sheet**

**H0,5/14S W**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

**Drawing**

