

H4,0/22D ZH GR SV**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com



- in multi-pack bag (5 x 100 pcs.)
- DIN colour code
- other colour code

General ordering data

| | |
|------------|---|
| Version | Wire-end ferrule, Twin wire-end ferrule, 15 mm, 12 mm, grey |
| Order No. | 9004730000 |
| Type | H4,0/22D ZH GR SV |
| GTIN (EAN) | 4008190161811 |
| Qty. | 100 pc(s). |
| Packaging | Multipack bag |

H4,0/22D ZH GR SV

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Technical data**Dimensions and weights**

Net weight 0.54 g

Technical data

Description of article Twin wire end ferrule, grey Version Twin wire-end ferrule

Wire-end ferrules

Collar height (A) 9 mm Collar width (B) 5.2 mm

Colour code DIN Conductor cross-section 4 mm²

Contact surface diameter (D1) 3.5 mm Contact surface length (L2) 12 mm

L1 in mm 22 mm Metal sleeve thickness (S1) 0.2 mm

Plastic collar thickness (S2) 0.5 mm Stripping length 15 mm

Wire connection cross section AWG, max. AWG 12

Classifications

ETIM 6.0 EC000005 ETIM 7.0 EC000005

ETIM 8.0 EC000005 ECLASS 9.0 27-40-02-01

ECLASS 9.1 27-40-02-01 ECLASS 10.0 27-40-02-01

ECLASS 11.0 27-40-02-01 ECLASS 12.0 27-40-02-01

Approvals

Approvals



ROHS Conform

UL File Number Search UL Website

Certificate no. (cULus) E499744

DownloadsEngineering Data [CAD data – STEP](#)Engineering Data [WSCAD, Zuken E3.S](#)User Documentation [Technical information - EN](#)[Technical information - DE](#)Catalogues [Catalogues in PDF-format](#)

Brochures

H4,0/22D ZH GR SV

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

Drawings

Drawing

