

PZ 1.5**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Crimping tools for wire end ferrules, with and without plastic collars**

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation

General ordering data

Version	Pressing tool, Crimping tool for wire-end ferrules, 0.14mm ² , 1.5mm ² , Trapezoidal crimp
Order No.	9005990000
Type	PZ 1.5
GTIN (EAN)	4008 190085964
Qty.	1 pc(s).
Replacement parts	9202810000

Creation date March 3, 2023 5:19:11 PM CET

Catalogue status 18.02.2023 / We reserve the right to make technical changes.

PZ 1.5

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Width	170 mm	Width (inches)	6.693 inch
Net weight	171.171 g		

Technical data

Description of article	Crimping tool for wire end ferrules with/without plastic collar, 0.14 to 6 mm ²	Version	Mechanical, without interchangeable inserts
------------------------	--	---------	---

Description of contact

Conductor cross-section, min. AWG	AWG 26	Crimping range, max.	1.5 mm ²
Crimping range, min.	0.14 mm ²	Type of contact	Wire-end ferrules with/without plastic collars

tool data crimping

Crimping type/profile	Trapezoidal crimp	Wire end ferrules cross-section, max.	1.5 mm ²
Wire end ferrules cross-section, min.	0.25 mm ²		

Classifications

ETIM 6.0	EC000168	ETIM 7.0	EC000168
ETIM 8.0	EC000168	ECLASS 9.0	21-04-38-11
ECLASS 9.1	21-04-38-11	ECLASS 10.0	21-04-38-11
ECLASS 11.0	21-04-38-11	ECLASS 12.0	21-04-38-11

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	2159813b-98fd-4068-b62a-bc89a046c012

Approvals

Approvals



Downloads

Engineering Data	WSCAD
User Documentation	Manual
Catalogues	Catalogues in PDF-format
Brochures	

PZ 1.5

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

