

CTN 25 D4**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Crimping tools for non-insulated connectors**

Rolled cable lugs, tubular cable lugs, terminal pins, parallel and serial connectors

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation

General ordering data

Version	Pressing tool, Crimping tool for contacts, 10mm ² , 25mm ² , Indent crimp
Order No.	9006220000
Type	CTN 25 D4
GTIN (EAN)	4008 190198633
Qty.	1 pc(s).
Replacement parts	1121010000

Creation date February 28, 2023 4:27:27 PM CET

CTN 25 D4

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Width	250 mm	Width (inches)	9.842 inch
Net weight	653.78 g		

Technical data

Description of article	Crimping tool for non-insulated connectors, 10-25 mm ²	Version	Mechanical, without interchangeable inserts
------------------------	---	---------	---

Description of contact

Conductor cross-section, min. AWG	AWG 8	Crimping range, max.	25 mm ²
Crimping range, min.	10 mm ²	Type of contact	Uninsulated connection

tool data crimping

Copper connector (rolled), max.	25 mm ²	Copper connector (rolled), min.	10 mm ²
Crimping profile 1, min.	10 mm ²	Crimping profile 2, min.	16 mm ²
Crimping profile 3, min.	25 mm ²	Crimping type/profile	Indent crimp

Classifications

ETIM 6.0	EC000168	ETIM 7.0	EC000168
ETIM 8.0	EC000168	ECLASS 9.0	21-04-38-11
ECLASS 9.1	21-04-38-11	ECLASS 10.0	21-04-38-11
ECLASS 11.0	21-04-38-11	ECLASS 12.0	21-04-38-11

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	2159813b-98fd-4068-b62a-bc89a046c012

Approvals

Approvals



Downloads

User Documentation	Manual
Catalogues	Catalogues in PDF-format
Brochures	

Data sheet

CTN 25 D4

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

