

**H1,5/19,5X SW SV****Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com



- In multi-pack bag
- Weidmüller colour code

**General ordering data**

Version	Wire-end ferrule, Standard, 15 mm, 10 mm, black
Order No.	<a href="#">9006630000</a>
Type	H1,5/19,5X SW SV
GTIN (EAN)	4008190332266
Qty.	100 pc(s).
Packaging	Multipack bag

**H1,5/19,5X SW SV**

**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

[info@weidmueller.com](mailto:info@weidmueller.com)

[www.weidmueller.com](http://www.weidmueller.com)

**Technical data**

**Dimensions and weights**

Net weight	0.26 g	
------------	--------	--

**Technical data**

Description of article	Wire end ferrule for short-circuit-proof and earth-fault-proof lines, black	Version	Standard
------------------------	---	---------	----------

**Wire-end ferrules**

Collar diameter (D2)	6.8 mm	Colour code	Weidmüller
Conductor cross-section	1.5 mm <sup>2</sup>	Contact surface diameter (D1)	1.8 mm
Contact surface length (L2)	10 mm	L1 in mm	19.5 mm
Metal sleeve thickness (S1)	0.15 mm	Plastic collar thickness (S2)	0.3 mm
Stripping length	15 mm	Wire connection cross section AWG, max.	AWG 16

**Classifications**

ETIM 6.0	EC000005	ETIM 7.0	EC000005
ETIM 8.0	EC000005	ECLASS 9.0	27-40-02-01
ECLASS 9.1	27-40-02-01	ECLASS 10.0	27-40-02-01
ECLASS 11.0	27-40-02-01	ECLASS 12.0	27-40-02-01

**Approvals**

Approvals



ROHS Conform

**Downloads**

Engineering Data	<a href="#">CAD data – STEP</a>
Engineering Data	<a href="#">WSCAD, Zuken E3.S</a>
User Documentation	<a href="#">Technical information - EN</a> <a href="#">Technical information - DE</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	

**Data sheet**

**H1,5/19,5X SW SV**

**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

**Drawings**

**Drawing**

