

**H4,0/19,5X GR SV****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



- Polypropylene conical cable entry
  - Heat-resistant up to 105°C
- for conductors from 1.5 to 16 mm<sup>2</sup> (AWG 16-6)  
tin-plated copper  
dimensional tolerances to DIN 46228 part 4

**General ordering data**

Version	Wire-end ferrule, Standard, 14 mm, 10 mm, grey
Order No.	<a href="#">9006750000</a>
Type	H4,0/19,5X GR SV
GTIN (EAN)	4008 190332297
Qty.	100 pc(s).
Packaging	Multipack bag

Creation date February 23, 2023 1:32:13 PM CET

Catalogue status 18.02.2023 / We reserve the right to make technical changes.

**H4,0/19,5X GR SV****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Dimensions and weights**

Net weight 0.37 g

**Technical data**

Description of article	Wire end ferrule for short-circuit-proof and earth-fault-proof lines, grey	Version	Standard
------------------------	--	---------	----------

**Wire-end ferrules**

Collar diameter (D2)	7.8 mm	Colour code	Weidmüller
Conductor cross-section	4 mm <sup>2</sup>	Contact surface diameter (D1)	2.9 mm
Contact surface length (L2)	10 mm	L1 in mm	19.5 mm
Metal sleeve thickness (S1)	0.2 mm	Plastic collar thickness (S2)	0.3 mm
Stripping length	14 mm	Wire connection cross section AWG, max.	AWG 12

**Classifications**

ETIM 6.0	EC000005	ETIM 7.0	EC000005
ETIM 8.0	EC000005	ECLASS 9.0	27-40-02-01
ECLASS 9.1	27-40-02-01	ECLASS 10.0	27-40-02-01
ECLASS 11.0	27-40-02-01	ECLASS 12.0	27-40-02-01

**Approvals**

Approvals



ROHS Conform

**Downloads**

Engineering Data	<a href="#">CAD data – STEP</a>
Engineering Data	<a href="#">WSCAD, Zuken E3.S</a>
User Documentation	<a href="#">Technical information - EN</a> <a href="#">Technical information - DE</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	

**Data sheet**

**H4,0/19,5X GR SV**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

**Drawing**

