

LG DMS PRO/ DMS 3**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Weidmüller torque screwdrivers have an ergonomic design and are therefore ideal for use with one hand. They can be used without causing fatigue in all installation positions. Apart from that, they incorporate an automatic torque limiter and have a good reproducibility accuracy.

General ordering data

Version	DMS 3, 90 % bei 3x 500 V AC / > 91 % bei 3 x 400 V AC
Order No.	9007460000
Type	LG DMS PRO/ DMS 3
GTIN (EAN)	4008 190404970
Qty.	1 Stück

Erstellungs-Datum June 1, 2023 12:25:41 PM CEST

Katalogstand 26.05.2023 / Technische Änderungen vorbehalten

LG DMS PRO/ DMS 3

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Net weight 604.79 g

Technical data

Charging time	Description of article	Mains-operated torque screwdriver with 1/4" drive
30 min		

Electric screwdriver

Battery voltage	3.6 V	Bit holder	1/4" DIN 3126 Form E6.3
Charger input	AC 220-240V~ 50-60Hz 30W	Charger output	DC 2.8...6V; 4.8A / 30W max.
Charging time	30 min	Idling speed	200 u. 600 min ⁻¹
Max. coupling torque	3 Nm	Rated voltage	3.6 V
Weight	600 g	Weight of charger	600 g

Classifications

ETIM 6.0	EC000359	ETIM 7.0	EC000359
ETIM 8.0	EC000359	ECLASS 9.1	21-05-92-01
ECLASS 10.0	21-05-92-01	ECLASS 11.0	21-05-29-01
ECLASS 12.0	21-05-29-01		

Environmental Product Compliance

REACH SVHC Lead 7439-92-1

Approvals

Approvals



ROHS Conform

Downloads

Catalogues [Catalogues in PDF-format](#)

Brochures