

SDIZ 0.6X3.5X100**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



VDE insulated slot-head screwdriver, SDI DIN 7437, ISO 2380/2, drive output acc. to DIN 5264, ISO 2380/1.
SoftFinish grip

General ordering data

Version	Screwdriver, Blade width (B): 3.5 mm, Blade length: 100 mm, Blade thickness (A): 0.6 mm
Order No.	9008450000
Type	SDIZ 0.6X3.5X100
GTIN (EAN)	4032248056446
Qty.	1 pc(s).
Delivery status	This article will no longer be available in the future.
Available until	2021-09-29
Alternative product	2749980000

Creation date February 28, 2023 9:13:53 AM CET

Catalogue status 18.02.2023 / We reserve the right to make technical changes.

SDIZ 0.6X3.5X100**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Width	205 mm	Width (inches)	8.071 inch
Net weight	35.9 g		

Technical data

Description of article	VDE-insulated screwdriver with pilot tip 0.6 x 3.5 x 100
------------------------	--

Screwing tools

Blade length	100 mm	Blade thickness (A)	0.6 mm
Blade width (B)	3.5 mm	Form	Slotted with pilot tip

Classifications

ETIM 6.0	EC000149	ETIM 7.0	EC000149
ETIM 8.0	EC000149	ECLASS 9.0	21-04-50-03
ECLASS 9.1	21-04-04-90	ECLASS 10.0	21-04-50-03
ECLASS 11.0	21-04-50-03	ECLASS 12.0	21-04-50-03

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Approvals

Approvals

**Downloads**

Approval/Certificate/Document of Conformity	Manufacturer's Declaration - Screwdrivers
Catalogues	Catalogues in PDF-format
Brochures	