

SDIZ 0.8X4.0X100**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



VDE insulated slot-head screwdriver, SDI DIN 7437, ISO 2380/2, drive output acc. to DIN 5264, ISO 2380/1.
SoftFinish grip

General ordering data

Version	Screwdriver, Blade width (B): 4 mm, Blade length: 100 mm, Blade thickness (A): 0.8 mm
Order No.	9008460000
Type	SDIZ 0.8X4.0X100
GTIN (EAN)	4032248056453
Qty.	1 pc(s).
Delivery status	This article will no longer be available in the future.
Available until	2021-12-31
Alternative product	2749990000

Creation date February 27, 2023 4:06:28 PM CET

Catalogue status 18.02.2023 / We reserve the right to make technical changes.

SDIZ 0.8X4.0X100**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Width	210 mm	Width (inches)	8.268 inch
Net weight	56.8 g		

Technical data

Description of article	VDE-insulated screwdriver with pilot tip 0.8 x 4.0 x 100
------------------------	--

Screwing tools

Blade length	100 mm	Blade thickness (A)	0.8 mm
Blade width (B)	4 mm	Form	Slotted with pilot tip

Classifications

ETIM 6.0	EC000149	ETIM 7.0	EC000149
ETIM 8.0	EC000149	ECLASS 9.0	21-04-50-03
ECLASS 9.1	21-04-04-90	ECLASS 10.0	21-04-50-03
ECLASS 11.0	21-04-50-03	ECLASS 12.0	21-04-50-03

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Approvals

Approvals

**Downloads**

Approval/Certificate/Document of Conformity	Manufacturer's Declaration - Screwdrivers
Catalogues	Catalogues in PDF-format
Brochures	