

HTG 58/59**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Crimping tools for coaxial connectors**

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation

General ordering data

Version	Pressing tool, Crimping tool for contacts, Hexagonal crimp
Order No.	9012020000
Type	HTG 58/59
GTIN (EAN)	4008 1900 18207
Qty.	1 pc(s).

Creation date February 28, 2023 5:04:04 PM CET

Catalogue status 18.02.2023 / We reserve the right to make technical changes.

HTG 58/59

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Dimensions and weights

Width	200 mm	Width (inches)	7.874 inch
Net weight	418.7 g		

Technical data

Description of article	Crimping tool for coaxial connectors BNC, TNC / AF 5.4/6.48	Version	Mechanical, without interchangeable inserts
------------------------	---	---------	---

Description of contact

Type of contact	Coaxial connector
-----------------	-------------------

tool data crimping

Crimping station, width (B 1)	10 mm	Crimping station, width (B 2)	10 mm
Crimping station, width (B 3)	2.3 mm	Crimping type/profile	Hexagonal crimp
Diameter of outer sleeve	6.2 mm	Hexagon AF (A)	5.4 mm
Hexagon spanner width (A 2)	6.48 mm	Hexagon spanner width (A 3)	1.72 mm
Internal contact diameter (D)	2 mm		

Classifications

ETIM 6.0	EC000168	ETIM 7.0	EC000168
ETIM 8.0	EC000168	ECLASS 9.0	21-04-38-11
ECLASS 9.1	21-04-38-11	ECLASS 10.0	21-04-38-11
ECLASS 11.0	21-04-38-11	ECLASS 12.0	21-04-38-11

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	2159813b-98fd-4068-b62a-bc89a046c012

Approvals

Approvals



Downloads

User Documentation	Manual
Catalogues	Catalogues in PDF-format
Brochures	

Data sheet

HTG 58/59

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

