

HTG 174**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Crimping tools for coaxial connectors**

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation

General ordering data

Version	Pressing tool, Crimping tool for contacts, Hexagonal crimp
Order No.	9012410000
Type	HTG 174
GTIN (EAN)	4008 190009434
Qty.	1 pc(s).

Creation date February 28, 2023 6:19:01 PM CET

Catalogue status 18.02.2023 / We reserve the right to make technical changes.

HTG 174

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Width	200 mm	Width (inches)	7.874 inch
Net weight	449 g		

Technical data

Description of article	Crimping tool for coaxial connectors BNC, TNC and N / AF 4.52	Version	Mechanical, without interchangeable inserts
------------------------	---	---------	---

Description of contact

Type of contact	Coaxial connector
-----------------	-------------------

tool data crimping

Crimping station, width (B 1)	10 mm	Crimping station, width (B 2)	2.3 mm
Crimping type/profile	Hexagonal crimp	Diameter of outer sleeve	5.4 mm
Hexagon AF (A)	4.52 mm	Hexagon spanner width (A 2)	1.72 mm
Internal contact diameter (D)	2 mm		

Classifications

ETIM 6.0	EC000168	ETIM 7.0	EC000168
ETIM 8.0	EC000168	ECLASS 9.0	21-04-38-11
ECLASS 9.1	21-04-38-11	ECLASS 10.0	21-04-38-11
ECLASS 11.0	21-04-38-11	ECLASS 12.0	21-04-38-11

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	2159813b-98fd-4068-b62a-bc89a046c012

Approvals

Approvals



Downloads

User Documentation	Manual
Catalogues	Catalogues in PDF-format
Brochures	

HTG 174

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

