

HTF ZRV**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Crimping tools for for turned/stamped contact**

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation
- With stop for exact positioning of the contacts.

General ordering data

Version	Pressing tool, Crimping tool for contacts, 0.2mm ² , 1mm ² , FoderBcrimp
Order No.	9014840000
Type	HTF ZRV
GTIN (EAN)	4008 190949969
Qty.	1 pc(s).

Creation date February 23, 2023 11:54:16 AM CET

Catalogue status 18.02.2023 / We reserve the right to make technical changes.

HTF ZRV

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Width	200 mm	Width (inches)	7.874 inch
Net weight	452.7 g		

Technical data

Description of article	Crimping tools for ZRV or MKF flat-blade contacts	Version	Mechanical, without interchangeable inserts
------------------------	---	---------	---

Description of contact

Conductor cross-section, min. AWG	AWG 24	Crimping range, max.	1 mm ²
Crimping range, min.	0.2 mm ²	Type of contact	Weidmüller ZRV

tool data crimping

Crimping profile 1, max.	0.35 mm ²	Crimping profile 1, min.	0.2 mm ²
Crimping profile 2, max.	1 mm ²	Crimping profile 2, min.	0.5 mm ²
Crimping type/profile	FoderBcrimp	Wire end ferrules cross-section, max.	1 mm ²
Wire end ferrules cross-section, min.	0.2 mm ²		

Classifications

ETIM 6.0	EC000168	ETIM 7.0	EC000168
ETIM 8.0	EC000168	ECLASS 9.0	21-04-38-11
ECLASS 9.1	21-04-38-11	ECLASS 10.0	21-04-38-11
ECLASS 11.0	21-04-38-11	ECLASS 12.0	21-04-38-11

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	2159813b-98fd-4068-b62a-bc89a046c012

Approvals

Approvals



Downloads

Catalogues	Catalogues in PDF-format
Brochures	

