

FLECAFIX 11/24**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Screwing tool for fixing and loosening cable glands and accessories in the sizes 11-36 AF.

- Can reach over several rows of glands
- No deforming of the cable glands
- Spanner size 11 to 36 mm
- Infinite adjustment of spanner size
- Ratchet function: not necessary to remove tool between turns
- Authentic one-hand tool

General ordering data

Version	Cable gland tool
Order No.	9015900000
Type	FLECAFIX 11/24
GTIN (EAN)	4032248309573
Qty.	1 pc(s).

Creation date February 23, 2023 4:29:23 PM CET

Catalogue status 18.02.2023 / We reserve the right to make technical changes.

FLECAFIX 11/24**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Depth	30 mm	Depth (inches)	1.181 inch
Height	60 mm	Height (inches)	2.362 inch
Width	190 mm	Width (inches)	7.48 inch
Net weight	173.45 g		

Technical data

Description of article	Cable gland tool, 11-24 AF
------------------------	----------------------------

Screwing tools

Size	11 - 24 mm
------	------------

Classifications

ETIM 6.0	EC000149	ETIM 7.0	EC000149
ETIM 8.0	EC000149	ECLASS 9.0	21-04-50-03
ECLASS 9.1	21-01-90-90	ECLASS 10.0	21-04-50-03
ECLASS 11.0	21-04-50-03	ECLASS 12.0	21-04-50-03

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	b28ab223-64ec-44cf-adb0-4dd6ebcae141

Approvals

Approvals

**Downloads**

User Documentation	Manual
Catalogues	Catalogues in PDF-format
Brochures	

FLECAFIX 11/24

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Example of use

