

## H2,5/19T ZH GR SV

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com



- in multi-pack bag (5 x 100 pcs.)
- DIN colour code
- other colour code

### General ordering data

Version	Wire-end ferrule, Twin wire-end ferrule, 13 mm, 10 mm, grey
Order No.	<a href="#">9018580000</a>
Type	H2,5/19T ZH GR SV
GTIN (EAN)	4008 190272647
Qty.	250 pc(s).
Packaging	Multipack bag

Creation date February 28, 2023 3:05:20 PM CET

Catalogue status 18.02.2023 / We reserve the right to make technical changes.

**H2,5/19T ZH GR SV****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Dimensions and weights**

Net weight 0.324 g

**Technical data**

Description of article Twin wire end ferrule, grey Version Twin wire-end ferrule

**Wire-end ferrules**

Collar height (A) 8 mm Collar width (B) 4.5 mm

Colour code Telemecanique Conductor cross-section 2.5 mm<sup>2</sup>

Contact surface diameter (D1) 2.8 mm Contact surface length (L2) 10 mm

L1 in mm 19 mm Metal sleeve thickness (S1) 0.15 mm

Plastic collar thickness (S2) 0.4 mm Stripping length 13 mm

Wire connection cross section AWG, max. AWG 14

**Classifications**

ETIM 6.0 EC000005 ETIM 7.0 EC000005

ETIM 8.0 EC000005 ECLASS 9.0 27-40-02-01

ECLASS 9.1 27-40-02-01 ECLASS 10.0 27-40-02-01

ECLASS 11.0 27-40-02-01 ECLASS 12.0 27-40-02-01

**Approvals**

Approvals



ROHS Conform

UL File Number Search UL Website

Certificate no. (cULus) E499744

**Downloads**Engineering Data [CAD data – STEP](#)Engineering Data [WSCAD, Zuken E3.S](#)User Documentation [Technical information - EN](#)[Technical information - DE](#)Catalogues [Catalogues in PDF-format](#)

Brochures

**Data sheet**

**H2,5/19T ZH GR SV**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

**Drawing**

