

**H4,0/26D GR****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



- supplied loose in polybag
- DIN colour code
- other colour code

**General ordering data**

Version	Wire-end ferrule, Standard, 20 mm, 18 mm, grey
Order No.	<a href="#">9019210000</a>
Type	H4,0/26D GR
GTIN (EAN)	4008 190002336
Qty.	100 pc(s).
Packaging	loose

Creation date February 17, 2023 12:49:21 PM CET

Catalogue status 03.02.2023 / We reserve the right to make technical changes.

**H4,0/26D GR**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data****Dimensions and weights**

Net weight 0.38 g

**Technical data**

Description of article	Wire end ferrule with plastic collar, grey	Version	Standard
------------------------	--	---------	----------

**Wire-end ferrules**

Collar diameter (D2)	4.8 mm	Colour code	DIN
Conductor cross-section	4 mm <sup>2</sup>	Contact surface diameter (D1)	2.8 mm
Contact surface length (L2)	18 mm	L1 in mm	26 mm
Metal sleeve thickness (S1)	0.2 mm	Military designation	T 20A 021 A
Plastic collar thickness (S2)	0.3 mm	Stripping length	20 mm
Wire connection cross section AWG, max.	AWG 12		

**Classifications**

ETIM 6.0	EC000005	ETIM 7.0	EC000005
ETIM 8.0	EC000005	ECLASS 9.0	27-40-02-01
ECLASS 9.1	27-40-02-01	ECLASS 10.0	27-40-02-01
ECLASS 11.0	27-40-02-01	ECLASS 12.0	27-40-02-01

**Approvals**

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E499744

**Downloads**

Engineering Data	<a href="#">CAD data – STEP</a>
Engineering Data	<a href="#">WSCAD, Zuken E3.S</a>
User Documentation	<a href="#">Technical information - EN</a> <a href="#">Technical information - DE</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	

**Data sheet**

**H4,0/26D GR**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

**Drawing**

