

H0,25/12T GE

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



- supplied loose in polybag
- Weidmüller colour code

General ordering data

Version	Wire-end ferrule, Standard, 10 mm, 8 mm, yellow
Order No.	9021020000
Type	H0,25/12T GE
GTIN (EAN)	4008190184230
Qty.	500 pc(s).
Packaging	loose

Creation date March 3, 2023 4:32:55 PM CET

Catalogue status 18.02.2023 / We reserve the right to make technical changes.

H0,25/12T GE**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Net weight 0.05 g

Technical data

Description of article	Wire end ferrule with plastic collar, yellow	Version	Standard
------------------------	--	---------	----------

Wire-end ferrules

Collar diameter (D2)	1.8 mm	Colour code	Telemecanique
Conductor cross-section	0.25 mm ²	Contact surface diameter (D1)	0.8 mm
Contact surface length (L2)	8 mm	L1 in mm	12 mm
Metal sleeve thickness (S1)	0.15 mm	Plastic collar thickness (S2)	0.25 mm
Stripping length	10 mm	Wire connection cross section AWG, max.	AWG 24

Classifications

ETIM 6.0	EC000005	ETIM 7.0	EC000005
ETIM 8.0	EC000005	ECLASS 9.0	27-40-02-01
ECLASS 9.1	27-40-02-01	ECLASS 10.0	27-40-02-01
ECLASS 11.0	27-40-02-01	ECLASS 12.0	27-40-02-01

Approvals

Approvals



ROHS

Conform

Downloads

Engineering Data	CAD data – STEP
Engineering Data	WSCAD, Zuken E3.S
User Documentation	Technical information - EN Technical information - DE
Catalogues	Catalogues in PDF-format
Brochures	

Data sheet

H0,25/12T GE

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Drawing

