

H25,0/30T SW

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



- supplied loose in poly-bag
- Weidmüller colour code
- DIN colour code
- other colour code

General ordering data

Version	Wire-end ferrule, Standard, 18 mm, 16 mm, black
Order No.	9021190000
Type	H25,0/30T SW
GTIN (EAN)	4008190115166
Qty.	50 pc(s).
Packaging	loose

Creation date March 1, 2023 1:36:08 PM CET

Catalogue status 18.02.2023 / We reserve the right to make technical changes.

H25,0/30T SW**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Net weight 1.16 g

Technical data

Description of article	Wire end ferrule with plastic collar, black	Version	Standard
------------------------	---	---------	----------

Wire-end ferrules

Collar diameter (D2)	11.2 mm	Colour code	Telemecanique
Conductor cross-section	25 mm ²	Contact surface diameter (D1)	7.3 mm
Contact surface length (L2)	16 mm	L1 in mm	30 mm
Metal sleeve thickness (S1)	0.2 mm	Military designation	T 20A 030 A
Plastic collar thickness (S2)	0.4 mm	Stripping length	18 mm
Wire connection cross section AWG, max.	AWG 3		

Classifications

ETIM 6.0	EC000005	ETIM 7.0	EC000005
ETIM 8.0	EC000005	ECLASS 9.0	27-40-02-01
ECLASS 9.1	27-40-02-01	ECLASS 10.0	27-40-02-01
ECLASS 11.0	27-40-02-01	ECLASS 12.0	27-40-02-01

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E499744

Downloads

Engineering Data	CAD data – STEP
Engineering Data	WSCAD, Zuken E3.S
User Documentation	Technical information - EN Technical information - DE
Catalogues	Catalogues in PDF-format
Brochures	

Data sheet

H25,0/30T SW

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Drawing

