

H0,34/10 TK

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



- supplied loose in polybag
- Weidmüller colour code

General ordering data

Version	Wire-end ferrule, Standard, 8 mm, 6 mm, Turquoise
Order No.	9025750000
Type	H0,34/10 TK
GTIN (EAN)	4008 190105365
Qty.	500 pc(s).
Packaging	loose

Creation date February 15, 2023 4:54:01 PM CET

Catalogue status 03.02.2023 / We reserve the right to make technical changes.

H0,34/10 TK

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Net weight	0.04 g
------------	--------

Technical data

Description of article	Wire end ferrule with plastic collar, turquoise	Version	Standard
------------------------	---	---------	----------

Wire-end ferrules

Collar diameter (D2)	2 mm	Colour code	Weidmüller
Conductor cross-section	0.34 mm ²	Contact surface diameter (D1)	0.8 mm
Contact surface length (L2)	6 mm	L1 in mm	10 mm
Metal sleeve thickness (S1)	0.15 mm	Plastic collar thickness (S2)	0.25 mm
Stripping length	8 mm	Wire connection cross section AWG, max.	AWG 22

Classifications

ETIM 6.0	EC000005	ETIM 7.0	EC000005
ETIM 8.0	EC000005	ECLASS 9.0	27-40-02-01
ECLASS 9.1	27-40-02-01	ECLASS 10.0	27-40-02-01
ECLASS 11.0	27-40-02-01	ECLASS 12.0	27-40-02-01

Approvals

Approvals



ROHS

Conform

Downloads

Engineering Data	CAD data – STEP
Engineering Data	WSCAD, Zuken E3.S
User Documentation	Technical information - EN Technical information - DE
Catalogues	Catalogues in PDF-format
Brochures	

Data sheet

H0,34/10 TK

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Drawing

