

## H0,34/10 TK SV

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



- in multipack bag (5 x 100 pcs.)
- Weidmüller colour code

### General ordering data

Version	Wire-end ferrule, Standard, 8 mm, 6 mm, Turquoise
Order No.	<a href="#">9026030000</a>
Type	H0,34/10 TK SV
GTIN (EAN)	4008 190177171
Qty.	500 pc(s).
Packaging	Multipack bag

Creation date February 15, 2023 5:00:53 PM CET

Catalogue status 03.02.2023 / We reserve the right to make technical changes.

## H0,34/10 TK SV

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

### Dimensions and weights

Net weight 0.054 g

### Technical data

Description of article	Wire end ferrule with plastic collar, turquoise	Version	Standard
------------------------	---	---------	----------

### Wire-end ferrules

Collar diameter (D2)	2 mm	Colour code	Weidmüller
Conductor cross-section	0.34 mm <sup>2</sup>	Contact surface diameter (D1)	0.8 mm
Contact surface length (L2)	6 mm	L1 in mm	10 mm
Metal sleeve thickness (S1)	0.15 mm	Plastic collar thickness (S2)	0.25 mm
Stripping length	8 mm	Wire connection cross section AWG, max.	AWG 22

### Classifications

ETIM 6.0	EC000005	ETIM 7.0	EC000005
ETIM 8.0	EC000005	ECLASS 9.0	27-40-02-01
ECLASS 9.1	27-40-02-01	ECLASS 10.0	27-40-02-01
ECLASS 11.0	27-40-02-01	ECLASS 12.0	27-40-02-01

### Approvals

Approvals



ROHS

Conform

### Downloads

Engineering Data	<a href="#">CAD data – STEP</a>
Engineering Data	<a href="#">WSCAD, Zuken E3.S</a>
User Documentation	<a href="#">Technical information - EN</a> <a href="#">Technical information - DE</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	

**Data sheet**

**H0,34/10 TK SV**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

**Drawing**

