

H70,0/37 GE**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030


32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com



- supplied loose in poly-bag
- Weidmüller colour code
- DIN colour code

General ordering data

Version	Wire-end ferrule, Standard, 26 mm, 21 mm, yellow
Order No.	9028200000
Type	H70,0/37 GE
GTIN (EAN)	4008190891572
Qty.	25 pc(s).
Packaging	loose

H70,0/37 GE

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Technical data**Dimensions and weights**

Net weight 3.9 g

Technical data

Description of article	Wire end ferrule with plastic collar, yellow	Version	Standard

Wire-end ferrules

Collar diameter (D2)	16 mm	Colour code	Weidmüller
Conductor cross-section	70 mm ²	Contact surface diameter (D1)	12.7 mm
Contact surface length (L2)	21 mm	L1 in mm	37 mm
Metal sleeve thickness (S1)	0.35 mm	Plastic collar thickness (S2)	0.6 mm
Stripping length	26 mm	Wire connection cross section AWG, max.	AWG 2/0

Classifications

ETIM 6.0	EC000005	ETIM 7.0	EC000005
ETIM 8.0	EC000005	ECLASS 9.0	27-40-02-01
ECLASS 9.1	27-40-02-01	ECLASS 10.0	27-40-02-01
ECLASS 11.0	27-40-02-01	ECLASS 12.0	27-40-02-01

Approvals

Approvals



ROHS

Conform

Downloads

Engineering Data	CAD data – STEP
Engineering Data	WSCAD, Zuken E3.S
User Documentation	Technical information - EN Technical information - DE
Catalogues	Catalogues in PDF-format
Brochures	

Data sheet

H70,0/37 GE

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

Drawings

Drawing

