


## H150,0/54 GE

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



- supplied loose in poly-bag
- Weidmüller colour code
- DIN colour code

### General ordering data

Version	Wire-end ferrule, Standard, 38 mm, 32 mm, yellow
Order No.	<a href="#">9028230000</a>
Type	H150,0/54 GE
GTIN (EAN)	4008190891602
Qty.	25 pc(s).
Packaging	loose

Creation date March 2, 2023 11:06:40 AM CET

Catalogue status 18.02.2023 / We reserve the right to make technical changes.

**H150,0/54 GE****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Dimensions and weights**

Net weight 10.8 g

**Technical data**

Description of article	Wire end ferrule with plastic collar, yellow	Version	Standard
------------------------	--	---------	----------

**Wire-end ferrules**

Collar diameter (D2)	23.5 mm	Colour code	Weidmüller
Conductor cross-section	150 mm <sup>2</sup>	Contact surface diameter (D1)	18.5 mm
Contact surface length (L2)	32 mm	L1 in mm	54 mm
Metal sleeve thickness (S1)	0.5 mm	Plastic collar thickness (S2)	0.75 mm
Stripping length	38 mm	Wire connection cross section AWG, max.	AWG 300 MCM

**Classifications**

ETIM 6.0	EC000005	ETIM 7.0	EC000005
ETIM 8.0	EC000005	ECLASS 9.0	27-40-02-01
ECLASS 9.1	27-40-02-01	ECLASS 10.0	27-40-02-01
ECLASS 11.0	27-40-02-01	ECLASS 12.0	27-40-02-01

**Approvals**

Approvals



ROHS

Conform

**Downloads**

Engineering Data	<a href="#">CAD data – STEP</a>
Engineering Data	<a href="#">WSCAD, Zuken E3.S</a>
User Documentation	<a href="#">Technical information - EN</a> <a href="#">Technical information - DE</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	

**Data sheet**

**H150,0/54 GE**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

**Drawing**

