

H0,14/10T BR SV**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



- Weidmüller colour code
- in multipack bag (5 x 100 pcs.)

General ordering data

Version	Wire-end ferrule, Standard, 8 mm, 6 mm, brown
Order No.	9028250000
Type	H0,14/10T BR SV
GTIN (EAN)	4008 190902018
Qty.	500 pc(s).
Packaging	Multipack bag

Creation date February 28, 2023 5:51:09 PM CET

Catalogue status 18.02.2023 / We reserve the right to make technical changes.

H0,14/10T BR SV**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Net weight 0.05 g

Technical data

Description of article	Wire end ferrule with plastic collar, brown	Version	Standard

Wire-end ferrules

Collar diameter (D2)	1.5 mm	Colour code	Telemecanique
Conductor cross-section	0.14 mm ²	Contact surface diameter (D1)	0.6 mm
Contact surface length (L2)	6 mm	L1 in mm	10 mm
Metal sleeve thickness (S1)	0.15 mm	Plastic collar thickness (S2)	0.25 mm
Stripping length	8 mm	Wire connection cross section AWG, max.	AWG 26

Classifications

ETIM 6.0	EC000005	ETIM 7.0	EC000005
ETIM 8.0	EC000005	ECLASS 9.0	27-40-02-01
ECLASS 9.1	27-40-02-01	ECLASS 10.0	27-40-02-01
ECLASS 11.0	27-40-02-01	ECLASS 12.0	27-40-02-01

Approvals

Approvals



ROHS

Conform

Downloads

Engineering Data	CAD data – STEP
Engineering Data	WSCAD, Zuken E3.S
User Documentation	Technical information - EN Technical information - DE
Catalogues	Catalogues in PDF-format
Brochures	

Data sheet

H0,14/10T BR SV

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Drawing

