

H4,0/14DS GR**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration

- Polypropylene conical cable entry funnel
 - Heat-resistant up to 105°C
- For conductors from 0.5 – 10.0 mm² (AWG 20-7)
Material: E-Cu, tin galvanised
Dimensional tolerance acc. to DIN 46228 sect. 4

General ordering data

Version	Wire-end ferrule, Standard, 10 mm, 8 mm, grey
Order No.	9028520000
Type	H4,0/14DS GR
GTIN (EAN)	4032248049035
Qty.	500 pc(s).
Packaging	loose

Creation date March 1, 2023 2:47:50 PM CET

Catalogue status 18.02.2023 / We reserve the right to make technical changes.

H4,0/14DS GR

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Net weight 0.222 g

Technical data

Description of article	Wire end ferrule with plastic collar, special size, grey	Version	Standard

Wire-end ferrules

Collar diameter (D2)	4.8 mm	Conductor cross-section	4 mm ²
Contact surface diameter (D1)	2.8 mm	Contact surface length (L2)	8 mm
L1 in mm	14 mm	Metal sleeve thickness (S1)	0.2 mm
Military designation	T 20A 023 A	Plastic collar thickness (S2)	0.3 mm
Stripping length	10 mm	Wire connection cross section AWG, max.	AWG 12

Classifications

ETIM 6.0	EC000005	ETIM 7.0	EC000005
ETIM 8.0	EC000005	ECLASS 9.0	27-40-02-01
ECLASS 9.1	27-40-02-01	ECLASS 10.0	27-40-02-01
ECLASS 11.0	27-40-02-01	ECLASS 12.0	27-40-02-01

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E499744

Downloads

Engineering Data	WSCAD
User Documentation	Technical information - EN Technical information - DE
Catalogues	Catalogues in PDF-format

Data sheet

H4,0/14DS GR

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Drawing

