


H2,5/16DS BL**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



- Polypropylene conical cable entry funnel
 - Heat-resistant up to 105°C
- For conductors from 0.5 – 10.0 mm² (AWG 20-7)
Material: E-Cu, tin galvanised
Dimensional tolerance acc. to DIN 46228 sect. 4

General ordering data

Version	Wire-end ferrule, Standard, 13 mm, 10 mm, blue
Order No.	9036220000
Type	H2,5/16DS BL
GTIN (EAN)	4032248068012
Qty.	500 pc(s).
Packaging	loose

Creation date February 28, 2023 6:00:18 PM CET

Catalogue status 18.02.2023 / We reserve the right to make technical changes.

H2,5/16DS BL

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Net weight 0.16 g

Technical data

Description of article	Wire end ferrule with plastic collar, special size, blue	Version	Standard

Wire-end ferrules

Collar diameter (D2)	4.2 mm	Colour code	Weidmüller
Conductor cross-section	2.5 mm ²	Contact surface diameter (D1)	2.2 mm
Contact surface length (L2)	10 mm	L1 in mm	16 mm
Metal sleeve thickness (S1)	0.15 mm	Plastic collar thickness (S2)	0.25 mm
Stripping length	13 mm	Wire connection cross section AWG, max.	AWG 14

Classifications

ETIM 6.0	EC000005	ETIM 7.0	EC000005
ETIM 8.0	EC000005	ECLASS 9.0	27-40-02-01
ECLASS 9.1	27-40-02-01	ECLASS 10.0	27-40-02-01
ECLASS 11.0	27-40-02-01	ECLASS 12.0	27-40-02-01

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (UR)	E354986

Downloads

Engineering Data	CAD data – STEP
Engineering Data	WSCAD
User Documentation	Technical information - EN Technical information - DE
Catalogues	Catalogues in PDF-format
Brochures	

Data sheet

H2,5/16DS BL

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Drawing

