

H0,75/16 ZH W**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



For the following conductors: 2 No. 0.75 mm² (2 No. AWG 18)

- supplied loose in poly-bag
- Weidmüller colour code
- DIN colour code
- other colour code

General ordering data

| | |
|------------|--|
| Version | Wire-end ferrule, Twin wire-end ferrule, 13 mm, 10 mm, white |
| Order No. | 9037240000 |
| Type | H0,75/16 ZH W |
| GTIN (EAN) | 4008 190492717 |
| Qty. | 500 pc(s). |
| Packaging | loose |

Creation date February 15, 2023 4:56:45 PM CET

Catalogue status 03.02.2023 / We reserve the right to make technical changes.

H0,75/16 ZH W

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Net weight 0.138 g

Technical data

| Description of article | Twin wire end ferrule, white | Version | Twin wire-end ferrule |
|------------------------|------------------------------|---------|-----------------------|
|------------------------|------------------------------|---------|-----------------------|

Wire-end ferrules

| | | | |
|---|------------|-----------------------------|----------------------|
| Collar height (A) | 5.5 mm | Collar width (B) | 3 mm |
| Colour code | Weidmüller | Conductor cross-section | 0.75 mm ² |
| Contact surface diameter (D1) | 1.7 mm | Contact surface length (L2) | 10 mm |
| L1 in mm | 16 mm | Metal sleeve thickness (S1) | 0.15 mm |
| Plastic collar thickness (S2) | 0.3 mm | Stripping length | 13 mm |
| Wire connection cross section AWG, max. | AWG 18 | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC000005 | ETIM 7.0 | EC000005 |
| ETIM 8.0 | EC000005 | ECLASS 9.0 | 27-40-02-01 |
| ECLASS 9.1 | 27-40-02-01 | ECLASS 10.0 | 27-40-02-01 |
| ECLASS 11.0 | 27-40-02-01 | ECLASS 12.0 | 27-40-02-01 |

Approvals

Approvals



| | |
|-------------------------|------------|
| ROHS | Conform |
| UL File Number Search | UL Website |
| Certificate no. (cULus) | E499744 |

Downloads

| | |
|--------------------|--|
| Engineering Data | CAD data – STEP |
| Engineering Data | WSCAD, Zuken E3.S |
| User Documentation | Technical information - EN Technical information - DE |
| Catalogues | Catalogues in PDF-format |
| Brochures | |

Data sheet

H0,75/16 ZH W

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Drawing

