


H16,0/29D ZH BL

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



- supplied loose in poly-bag
- Weidmüller colour code
- DIN colour code

General ordering data

Version	Wire-end ferrule, Twin wire-end ferrule, 20 mm, 16 mm, blue
Order No.	9037590000
Type	H16,0/29D ZH BL
GTIN (EAN)	4008 190493165
Qty.	50 pc(s).
Packaging	loose

Creation date February 27, 2023 4:14:50 PM CET

Catalogue status 18.02.2023 / We reserve the right to make technical changes.

H16,0/29D ZH BL**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Net weight 1.38 g

Technical data

Description of article Twin wire end ferrule, blue Version Twin wire-end ferrule

Wire-end ferrules

Collar height (A)	17.2 mm	Collar width (B)	9.5 mm
Colour code	DIN	Conductor cross-section	16 mm ²
Contact surface diameter (D1)	8.3 mm	Contact surface length (L2)	16 mm
L1 in mm	29 mm	Metal sleeve thickness (S1)	0.3 mm
Plastic collar thickness (S2)	0.6 mm	Stripping length	20 mm
Wire connection cross section AWG, max.	AWG 6		

Classifications

ETIM 6.0	EC000005	ETIM 7.0	EC000005
ETIM 8.0	EC000005	ECLASS 9.0	27-40-02-01
ECLASS 9.1	27-40-02-01	ECLASS 10.0	27-40-02-01
ECLASS 11.0	27-40-02-01	ECLASS 12.0	27-40-02-01

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E499744

Downloads

Engineering Data	CAD data – STEP
Engineering Data	WSCAD, Zuken E3.S
User Documentation	Technical information - EN Technical information - DE
Catalogues	Catalogues in PDF-format
Brochures	

Data sheet

H16,0/29D ZH BL

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Drawing

