

H6,0/23T ZH GN


Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



- supplied loose in poly-bag
- Weidmüller colour code
- DIN colour code
- other colour code

General ordering data

Version	Wire-end ferrule, Twin wire-end ferrule, 20 mm, 12 mm, green
Order No.	9037690000
Type	H6,0/23T ZH GN
GTIN (EAN)	4008 190493486
Qty.	100 Stück
Packaging	loose

Erstellungs-Datum May 25, 2023 11:23:26 AM CEST

Katalogstand 12.05.2023 / Technische Änderungen vorbehalten

H6,0/23T ZH GN

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Net weight 0.6 g

Technical data

Description of article	Twin wire end ferrule, green	Version	Twin wire-end ferrule
------------------------	------------------------------	---------	-----------------------

Wire-end ferrules

Collar height (A)	11.4 mm	Collar width (B)	6.2 mm
Colour code	Telemecanique	Conductor cross-section	6 mm ²
Contact surface diameter (D1)	4.5 mm	Contact surface length (L2)	12 mm
L1 in mm	23 mm	Metal sleeve thickness (S1)	0.2 mm
Plastic collar thickness (S2)	0.5 mm	Stripping length	20 mm
Wire connection cross section AWG, max.	AWG 10		

Classifications

ETIM 6.0	EC000005	ETIM 7.0	EC000005
ETIM 8.0	EC000005	ECLASS 9.0	27-40-02-01
ECLASS 9.1	27-40-02-01	ECLASS 10.0	27-40-02-01
ECLASS 11.0	27-40-02-01	ECLASS 12.0	27-40-02-01

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E499744

Downloads

Engineering Data	CAD data – STEP
Engineering Data	WSCAD, Zuken E3.S, EPLAN
User Documentation	Technical information - EN Technical information - DE
Catalogues	Catalogues in PDF-format
Brochures	

H6,0/23T ZH GN

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawing

