

**CRIMPER 6 I****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Crimping tools for insulated connectors**

cable lugs, terminal pins, parallel and serial connectors, plug-in connectors

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation
- With stop for exact positioning of the contacts.
- Tested to DIN EN 60352 part 2

**General ordering data**

Version	Tools, Crimping tool for contacts, 0.25mm <sup>2</sup> , 6mm <sup>2</sup>
Order No.	<a href="#">9040450000</a>
Type	CRIMPER 6 I
GTIN (EAN)	4008 19046 1515
Qty.	1 Stück

## CRIMPER 6 I

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technische Daten

### Dimensions and weights

Width	200 mm	Width (inches)	7.874 inch
Net weight	504.57 g		

### Technical data

Description of article	Crimping tool for insulated connectors, 0.5-6 mm <sup>2</sup>	Version	Mechanical, without interchangeable inserts
------------------------	---	---------	---

### Description of contact

Crimping range, max.	6 mm <sup>2</sup>	Crimping range, min.	0.25 mm <sup>2</sup>
Type of contact	Insulated connector		

### tool data crimping

Crimping profile 1, max.	1.5 mm <sup>2</sup>	Crimping profile 1, min.	0.5 mm <sup>2</sup>
Crimping profile 2, max.	2.5 mm <sup>2</sup>	Crimping profile 2, min.	1.1 mm <sup>2</sup>
Crimping profile 3, max.	6 mm <sup>2</sup>	Crimping profile 3, min.	2.6 mm <sup>2</sup>

### Classifications

ETIM 6.0	EC000168	ETIM 7.0	EC000168
ETIM 8.0	EC000168	ECLASS 9.0	21-04-38-11
ECLASS 9.1	21-04-38-11	ECLASS 10.0	21-04-38-11
ECLASS 11.0	21-04-38-11	ECLASS 12.0	21-04-38-11

### Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

### Approvals

Approvals

