

**CRIMPER 25 N D4****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Crimping tools for non-insulated connectors**

Rolled cable lugs, tubular cable lugs, terminal pins, parallel and serial connectors

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation

**General ordering data**

Version	Tools, Crimping tool for contacts, 10mm <sup>2</sup> , 25mm <sup>2</sup>
Order No.	<a href="#">9040460000</a>
Type	CRIMPER 25 N D4
GTIN (EAN)	4008 19046 1508
Qty.	1 Stück

Erstellungs-Datum May 25, 2023 11:02:12 AM CEST

Katalogstand 12.05.2023 / Technische Änderungen vorbehalten

## CRIMPER 25 N D4

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technische Daten

### Dimensions and weights

Width	250 mm	Width (inches)	9.842 inch
Net weight	550 g		

### Technical data

Description of article	Crimping tool for non-insulated connectors, 10-25 mm <sup>2</sup>	Version	Mechanical, without interchangeable inserts
------------------------	---	---------	---

### Description of contact

Crimping range, max.	25 mm <sup>2</sup>	Crimping range, min.	10 mm <sup>2</sup>
Type of contact	Uninsulated connection		

### tool data crimping

Crimping profile 1, max.	10 mm <sup>2</sup>	Crimping profile 2, max.	16 mm <sup>2</sup>
Crimping profile 3, max.	25 mm <sup>2</sup>		

### Classifications

ETIM 6.0	EC000168	ETIM 7.0	EC000168
ETIM 8.0	EC000168	ECLASS 9.0	21-04-38-11
ECLASS 9.1	21-04-38-11	ECLASS 10.0	21-04-38-11
ECLASS 11.0	21-04-38-11	ECLASS 12.0	21-04-38-11

### Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

### Approvals

Approvals



### Downloads

Catalogues	<a href="#">Catalogues in PDF-format</a>
------------	--