

CRIMPER 50 Z**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Crimping tools for wire end ferrules, with and without plastic collars**

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation

General ordering data

Version	Tools, Crimping tool for wire-end ferrules, 35mm ² , 50mm ²
Order No.	9040480000
Type	CRIMPER 50 Z
GTIN (EAN)	4008 19046 1492
Qty.	1 Stück

Erstellungs-Datum May 25, 2023 11:02:31 AM CEST

Katalogstand 12.05.2023 / Technische Änderungen vorbehalten

CRIMPER 50 Z

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Width	250 mm	Width (inches)	9.842 inch
Net weight	522.57 g		

Technical data

Description of article	Crimping tool for wire-end ferrules 35 - 50mm ²	Version	Mechanical, without interchangeable inserts
------------------------	--	---------	---

Description of contact

Crimping range, max.	50 mm ²	Crimping range, min.	35 mm ²
Type of contact	Wire-end ferrules with/without plastic collars		

tool data crimping

Crimping profile 1, max.	25 mm ²	Crimping profile 2, max.	35 mm ²
Crimping profile 3, max.	50 mm ²		

Classifications

ETIM 6.0	EC000168	ETIM 7.0	EC000168
ETIM 8.0	EC000168	ECLASS 9.0	21-04-38-11
ECLASS 9.1	21-04-38-11	ECLASS 10.0	21-04-38-11
ECLASS 11.0	21-04-38-11	ECLASS 12.0	21-04-38-11

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Approvals

Approvals



Downloads

Catalogues	Catalogues in PDF-format
------------	--