

CRIMPER 6 N**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Crimping tools for non-insulated connectors**

Rolled cable lugs, tubular cable lugs, terminal pins, parallel and serial connectors

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation

General ordering data

Version	Tools, Crimping tool for contacts, 0.5mm ² , 6mm ²
Order No.	9040520000
Type	CRIMPER 6 N
GTIN (EAN)	4008 19046 146 1
Qty.	1 Stück

CRIMPER 6 N

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Depth	30 mm	Depth (inches)	1.181 inch
Height	78 mm	Height (inches)	3.071 inch
Width	200 mm	Width (inches)	7.874 inch
Net weight	378.8 g		

Technical data

Description of article	Crimping tool for non-insulated connectors, 0.25-6 mm ²	Version	Mechanical, without interchangeable inserts
------------------------	--	---------	---

Description of contact

Crimping range, max.	6 mm ²	Crimping range, min.	0.5 mm ²
Type of contact	Uninsulated connection		

tool data crimping

Crimping profile 1, max.	1.5 mm ²	Crimping profile 1, min.	0.5 mm ²
Crimping profile 2, max.	2.5 mm ²	Crimping profile 2, min.	1.1 mm ²
Crimping profile 3, max.	6 mm ²	Crimping profile 3, min.	2.6 mm ²

Classifications

ETIM 6.0	EC000168	ETIM 7.0	EC000168
ETIM 8.0	EC000168	ECLASS 9.0	21-04-38-11
ECLASS 9.1	21-04-38-11	ECLASS 10.0	21-04-38-11
ECLASS 11.0	21-04-38-11	ECLASS 12.0	21-04-38-11

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Approvals

Approvals



Downloads

Catalogues [Catalogues in PDF-format](#)