

CRIMPER 16 Z**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Crimping tools for wire end ferrules, with and without plastic collars**

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation

General ordering data

Version	Tools, Crimping tool for wire-end ferrules, 6mm ² , 16mm ² , Trapezoidal crimp
Order No.	9040540000
Type	CRIMPER 16 Z
GTIN (EAN)	4008 19046 1447
Qty.	1 Stück

Erstellungs-Datum May 25, 2023 11:03:25 AM CEST

Katalogstand 12.05.2023 / Technische Änderungen vorbehalten

CRIMPER 16 Z

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Depth	30 mm	Depth (inches)	1.181 inch
Height	78 mm	Height (inches)	3.071 inch
Width	200 mm	Width (inches)	7.874 inch
Length	200 mm	Length (inches)	7.874 inch
Net weight	373.61 g		

Technical data

Description of article	Crimping tool for wire-end ferrules 6 - 16mm ²	Version	Mechanical, without interchangeable inserts
------------------------	---	---------	---

Description of contact

Crimping range, max.	16 mm ²	Crimping range, min.	6 mm ²
Type of contact	Wire-end ferrules with/without plastic collars		

tool data crimping

Crimping profile 1, max.	6 mm ²	Crimping profile 2, max.	10 mm ²
Crimping profile 3, max.	16 mm ²	Crimping type/profile	Trapezoidal crimp
Wire end ferrules cross-section, max.	16 mm ²	Wire end ferrules cross-section, min.	6 mm ²

Classifications

ETIM 6.0	EC000168	ETIM 7.0	EC000168
ETIM 8.0	EC000168	ECLASS 9.0	21-04-38-11
ECLASS 9.1	21-04-38-11	ECLASS 10.0	21-04-38-11
ECLASS 11.0	21-04-38-11	ECLASS 12.0	21-04-38-11

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Approvals

Approvals



Downloads

Catalogues [Catalogues in PDF-format](#)