

STRIPSY

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Sheathing stripper for PVC cables

General ordering data

Version	Sheathing strippers
Order No.	9042000000
Type	STRIPSY
GTIN (EAN)	4008 190337834
Qty.	1 pc(s).

Creation date March 1, 2023 2:46:20 PM CET

STRIPSY**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Depth	10 mm	Depth (inches)	0.394 inch
Height	46 mm	Height (inches)	1.811 inch
Width	97 mm	Width (inches)	3.819 inch
Net weight	54 g		

Technical data

Description of article	Stripping and cutting tool for data cable
------------------------	---

Stripping tools

Cable type	UTP and STP data cables	Copper cable - flexible, max.	4 mm ²
Cut depth	adjustable	Max. conductor diameter	12.5 mm
Min. conductor diameter	0.5 mm	Stripping range AWG, max.	11 AWG
Stripping range AWG, min.	20 AWG	Stripping range, min.	0.08 mm ²
UTP und STP data cables, max. diameter 8 mm			

Classifications

ETIM 6.0	EC000163	ETIM 7.0	EC000163
ETIM 8.0	EC000163	ECLASS 9.0	21-04-90-90
ECLASS 9.1	21-04-37-06	ECLASS 10.0	21-04-90-90
ECLASS 11.0	21-04-90-90	ECLASS 12.0	21-04-90-90

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	cf06c250-ed1e-4a45-9c1b-c5c8cbf13bf0

Approvals

Approvals

**Downloads**

Catalogues	Catalogues in PDF-format
------------	--