

CTIN CM 1.6/2.5

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

**Crimping tools for turned contacts**

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation
- With stop for exact positioning of the contacts.

General ordering data

Version	Pressing tool, Crimping tool for contacts, 0.14mm ² , 6mm ² , 4-indent crimp
Order No.	9205430000
Type	CTIN CM 1.6/2.5
GTIN (EAN)	4032248733446
Qty.	1 pc(s).

Creation date February 27, 2023 4:34:47 PM CET

Catalogue status 18.02.2023 / We reserve the right to make technical changes.

CTIN CM 1.6/2.5

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Width	230 mm	Width (inches)	9.055 inch
Net weight	1,175 g		

Technical data

Description of article	Crimping tool for HD, HE and ConCept M10/M5 contacts, 0.14-6 mm ²	Version	Mechanical, without interchangeable inserts
------------------------	--	---------	---

Description of contact

Conductor cross-section, min. AWG	AWG 26	Crimping range, max.	6 mm ²
Crimping range, min.	0.14 mm ²	Type of contact	Turned contacts

tool data crimping

Crimping profile 1, max.	6 mm ²	Crimping profile 1, min.	0.14 mm ²
Crimping type/profile	4-indent crimp		

Classifications

ETIM 6.0	EC000168	ETIM 7.0	EC000168
ETIM 8.0	EC000168	ECLASS 9.0	21-04-38-11
ECLASS 9.1	21-04-38-11	ECLASS 10.0	21-04-38-11
ECLASS 11.0	21-04-38-11	ECLASS 12.0	21-04-38-11

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Approvals

Approvals



Downloads

User Documentation	Manual_other languages Manual_DE_EN
Catalogues	Catalogues in PDF-format
Brochures	