

WK S 0,4X2,5**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

**Interchangeable bits for torque screwdriver**

Drive output acc. to DIN 5264, ISO 2380/1

General ordering data

Version	Screwdriver insert
Order No.	9918520000
Type	WK S 0,4X2,5
GTIN (EAN)	4032248388882
Qty.	1 Stück

WK S 0,4X2,5

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Technische Daten

Dimensions and weights

Depth	4 mm	Depth (inches)	0.157 inch
Height	4 mm	Height (inches)	0.157 inch
Width	175 mm	Width (inches)	6.89 inch
Net weight	21 g		

Technical data

Description of article	Interchangeable bit for slotted screws, size 0.4x2.5
------------------------	--

Screwing tools

Blade length	175 mm	Blade thickness (A)	0.4 mm
Blade width (B)	2.5 mm	Form	Slotted
Torque setting, max.	0.4 Nm		

Classifications

ETIM 6.0	EC002116	ETIM 7.0	EC002116
ETIM 8.0	EC003864	ECLASS 9.1	21-04-04-90
ECLASS 10.0	21-04-04-90	ECLASS 11.0	21-04-42-04
ECLASS 12.0	21-04-42-04		

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	6a3438d7-aa8c-48e4-8879-adf736ca79e3

Approvals

Approvals



Downloads

Catalogues	Catalogues in PDF-format
Brochures	