



Hinge Bases

-Side Mounting T-Shaped Type-

CAD Data

RoHS

H Dim. Specified Type		W, H Dim. Specified Type		□	S	A
H7 Type	H7 Type with Tap	H7 Type	H7 Type with Tap			
HKSBB	HKSBBT	HGSBB	HGSBBT	1.1191/C45E	Black Oxide	Set Screws 1 pc. (1.4301/ X5CrNi18-10)
HKSBM	HKSBMT	HGSBM	HGSBMT		Electroless Nickel Plating	
HKSBS	HKSBST	HGSBS	HGSBST		1.4301/X5CrNi18-10	-

25 / (√63 / 1.5)

H Dimension Specified Type

W, H Dimension Specified Type

⊙ For H7 Type, M part doesn't have tap and set screw. ⊙ Holes for D2 are drill holes, not counterbored.

H Dimension Specified Type

Part Number	Type	H 1mm Increment	W	A	F	B	K	T	d	d1	H1	M	Unit Price Qty. 1~4					
													HKSBB	HKSBM	HKSBS	HKSBBT	HKSBMT	HKSBST
2	(H7 Type)	15~20	4	13	7	H+3	6	6	-	-	-	-	18,40	20,30	26,60	-	-	-
3		15~25	6	16	8	H+5	10	9	3.5	6.5	3.5	M3	18,40	20,30	26,60	22,10	23,90	30,20
4			8	19	11	H+6	12	12	4.5	8	4.5	M4	18,40	20,30	26,60	22,10	23,90	30,20
5		20~30	10	25	16	H+8	14	14	5.5	9.5	5.5	M5	20,30	22,30	29,30	23,90	25,90	32,90
6			12	32	20	H+10	16	16	6.5	11	6.5	M6	20,30	22,30	29,30	23,90	25,90	32,90
8		25~35	16	38	26	H+12	18	18	7.5	12.5	7.5	M8	22,10	24,30	31,90	25,70	27,90	35,60
10			20	47	36	H+14	22	22	9.5	15.5	9.5	M10	22,10	24,30	31,90	25,70	27,90	35,60
12		30~40	25	58	47	H+17	28	28	12.5	19.5	12.5	M12	23,90	26,40	34,70	27,50	30,00	38,30
13			30	70	58	H+20	34	34	15.5	24.5	15.5	M14	23,90	26,40	34,70	27,50	30,00	38,30
14			35	82	70	H+24	41	41	19.5	30.5	19.5	M16	25,70	28,40	37,30	29,30	32,00	40,90
15		35~45	40	95	82	H+28	49	49	24.5	37.5	24.5	M20	27,60	30,40	39,90	31,20	34,00	43,50
16			45	110	95	H+34	59	59	30.5	45.5	30.5	M25	27,60	30,40	39,90	31,20	34,00	43,50
20		40~50	60	142	127	H+44	75	75	39.5	59.5	39.5	M30	33,20	36,50	48,10	36,80	40,10	51,70
25			75	177	162	H+57	95	95	49.5	75.5	49.5	M36	37,20	41,00	54,00	40,90	44,60	57,60

⊙ For detailed hinge pin dimension, refer to P.672.

W, H Dimension Specified Type

Part Number	Type	DH7	W 1mm Increment	H 5mm Increment	A	F	B	K	T	d	d1	H1	M	Unit Price Qty. 1~4					
														HGSBB	HGSBM	HGSBS	HGSBBT	HGSBMT	HGSBST
2	(H7 Type)	3~5	15~20	13	7	H+3	6	6	6	-	-	-	-	17,10	18,80	24,80	-	-	-
3		3~6	15~25	16	8	H+5	10	9	3.5	6.5	3.5	M3	17,10	18,80	24,80	20,70	22,40	28,40	
4		4~8		19	11	H+6	12	12	4.5	8	4.5	M4	17,10	18,80	24,80	20,70	22,40	28,40	
5		5~10	20~30	25	16	H+8	14	14	5.5	9.5	5.5	M5	18,80	20,70	27,20	22,40	24,40	30,80	
6		6~12		32	20	H+10	16	16	6.5	11	6.5	M6	18,80	20,70	27,20	22,40	24,40	30,80	
8		8~16	25~35	38	26	H+12	18	18	7.5	12.5	7.5	M8	20,50	22,60	29,60	24,10	26,20	33,30	
10		10~18		47	36	H+14	22	22	9.5	15.5	9.5	M10	20,50	22,60	29,60	24,10	26,20	33,30	
12		12~18	30~40	58	47	H+17	28	28	12.5	19.5	12.5	M12	22,20	24,50	32,20	25,80	28,20	35,80	
13		13~24		70	58	H+20	34	34	15.5	24.5	15.5	M14	22,20	24,50	32,20	25,80	28,20	35,80	
14		14~24		82	70	H+24	41	41	19.5	30.5	19.5	M16	23,90	26,40	34,60	27,50	30,00	38,30	
15		15~24	35~45	95	82	H+28	49	49	24.5	37.5	24.5	M20	25,70	28,20	37,00	29,30	31,80	40,60	
16		16~24		110	95	H+34	59	59	30.5	45.5	30.5	M25	25,70	28,20	37,00	29,30	31,80	40,60	
20		20~30	40~50	142	127	H+44	75	75	39.5	59.5	39.5	M30	30,70	33,90	44,60	34,40	37,50	48,20	
25		25~35		177	162	H+57	95	95	49.5	75.5	49.5	M36	34,40	38,00	49,90	38,50	42,00	53,90	

⊙ For detailed hinge pin dimension, refer to P.672. ⊙ For H7 type with tap, W≥M + 2 is required.

Order Part Number - H
Example HKSBB6 - H30

Price

Volume Discount P.92

Quantity	1~4	5~9	10~19	20~25
Rate	Price List	5%	10%	15%

⊙ For orders larger than indicated values, please request for quotation.

Part Number - W - H
HGSBB6 - W9 - H30

Days to Ship • H Dim. Specified Type
8 Days

• W, H Dimension Specified Type
10 Days 5,00 EUR/piece **P.92**

⊙ An Express Charge of 13,50 EUR for 3 or more identical pieces.



Hinge Bases

-Side Mounting U-Shaped Type-

CAD Data

RoHS

H Dimension Specified Type		W, H Dimension Specified Type		□	S	A
H7 Type	H7 Type with Tap	H7 Type	H7 Type with Tap			
HKSUB	HKSUBT	HGSUB	HGSUBT	1.1191/C45E	Black Oxide	Set Screws 2 pcs. (1.4301/ X5CrNi18-10)
HKSUM	HKSUMT	HGSUM	HGSUMT		Electroless Nickel Plating	
HKSUS	HKSUST	HGSUS	HGSUST		1.4301/X5CrNi18-10	-

25 / (√63 / 1.5)

H Dimension Specified Type

W, H Dimension Specified Type

⊙ For H7 Type, M part doesn't have tap and set screw. ⊙ Holes for D2 are drill holes, not counterbored.

H Dimension Specified Type

Part Number	Type	H 1mm Increment	W	A	F	B	K	T	d	d1	H1	M	Unit Price Qty. 1~4					
													HKSUB	HKSUM	HKSUS	HKSUBT	HKSUMT	HKSUST
2	(H7 Type)	15~20	4	13	7	H+3	6	6	-	-	-	-	18,80	20,40	27,40	-	-	-
3			6	16	8	H+5	10	9	3.5	6.5	3.5	M3	18,80	20,40	27,40	24,70	26,30	33,20
4		20~25	8	19	11	H+6	12	12	4.5	8	4.5	M4	18,80	20,40	27,40	24,70	26,30	33,20
5			10	25	16	H+8	14	14	5.5	9.5	5.5	M5	20,60	22,20	29,90	26,50	28,00	35,60
6		25~30	12	32	20	H+10	16	16	6.5	11	6.5	M6	20,60	22,20	29,90	26,50	28,00	35,60
8			16	38	26	H+12	18	18	7.5	12.5	7.5	M8	22,30	24,80	32,50	28,20	30,50	38,30
10			20	47	36	H+14	22	22	9.5	15.5	9.5	M10	22,30	24,80	32,50	28,20	30,50	38,30
12		30~40	25	58	47	H+17	28	28	12.5	19.5	12.5	M12	24,00	26,60	34,90	29,90	32,30	40,70
13			30	70	58	H+20	34	34	15.5	24.5	15.5	M14	25,70	28,40	37,40	31,60	34,20	43,10
14			35	82	70	H+24	41	41	19.5	30.5	19.5	M16	26,60	29,30	38,60	32,50	35,20	44,40
15		35~45	40	95	82	H+28	49	49	24.5	37.5	24.5	M20	27,50	30,30	39,80	33,40	36,20	45,60
16			45	110	95	H+34	59	59	30.5	45.5	30.5	M25	27,50	30,30	39,80	33,40	36,20	45,60
20		40~50	60	142	127	H+44	75	75	39.5	59.5	39.5	M30	32,60	36,00	47,30	38,40	41,80	53,10
25			75	177	162	H+57	95	95	49.5	75.5	49.5	M36	36,50	40,20	53,00	42,30	46,10	58,90

⊙ For detailed hinge pin dimension, refer to P.672.

W, H Dimension Specified Type

Part Number	Type	DH7	W 1mm Increment	H 5mm Increment	A	F	B	K	T	d	d1	H1	M	Unit Price Qty. 1~4					
														HGSUB	HGSUM	HGSUS	HGSUBT	HGSUMT	HGSUST
2	(H7 Type)	3~5	15~20	13	7	H+3	6	6	6	-	-	-	-	17,10	18,80	24,80	-	-	-
3		3~6	15~25	16	8	H+5	10	9	3.5	6.5	3.5	M3	17,10	18,80	24,80	22,90	24,60	30,60	
4		4~8		19	11	H+6	12	12	4.5	8	4.5	M4	17,10	18,80	24,80	20,70	22,40	28,40	
5		5~10	20~30	25	16	H+8	14	14	5.5	9.5	5.5	M5	20,50	22,60	29,60	26,30	28,40	35,50	
6		6~12		32	20	H+10	16	16	6.5	11	6.5	M6	20,50	22,60	29,60	26,30	28,40	35,50	
8		8~16	25~35	38	26	H+12	18	18	7.5	12.5	7.5	M8	22,20	24,50	32,20	28,00	30,30	38,00	
10		10~18		47	36	H+14	22	22	9.5	15.5	9.5	M10	22,20	24,50	32,20	28,00	30,30	38,00	
12		12~18	30~40	58	47	H+17	28	28	12.5	19.5	12.5	M12	23,90	26,40					