

Slide Rails

Medium Load, Steel, Stainless Steel

Load Rating: 225N~481N/2 pcs.


■Features: The rails are trivalent chrome coated steel. Economically priced slide rails compliant with RoHS regulations.

■Steel, Two-Step



RoHS10

SR36



Rail Disassembly: **Possible**

Inner and outer rails are not exchangeable.

M Material: Steel

S Surface Treatment: Bright Chromate (Trivalent Chromium)

Part Number		Rail Length	Stroke	A	B	C	D	E	F	G	Load Rating (N/2 pcs.)	Unit Price	Volume Discount Rate
Type	No.												
SR36	12	305	229	-	152.4	254	-	149.2	260.3	273	294	1 ~ 5 pc(s).	6 ~ 20 pcs
	14	356	279	-	203.2	304.8	-	200	311.1	323.8	363		
	16	406	305	-	254	355.6	-	250.8	361.9	374.6	382		
	18	457	330	203.2	304.8	406.4	212.7	301.6	412.7	425.4	362		
	20	508	381	228.6	355.6	457.2	238.1	352.4	463.5	476.2	323		
	22	559	406	254	406.4	508	263.5	403.2	514.3	527	304		
	24	610	432	279.4	457.2	558.8	288.9	454	565.1	577.8	265		
	26	660	483	304.8	508	609.6	314.3	504.8	615.9	628.6	235		
	28	711	508	330.2	558.8	660.4	339.7	555.6	666.7	679.4	225		

For horizontal installation, the target value of load rating is 25% (Reference Value).
The rails stop once in the full stroke position. The inner and outer rails can be separated by pulling further.


■Features: The rails are made of EN 1.4301 Equiv., which has excellent corrosion resistance.

■Stainless Steel, Two-Step



RoHS10

SSRN36



Rail Disassembly: **Not Possible**

Inner and outer rails are not exchangeable.

M Material: EN 1.4301 Equiv.

Ball: EN 1.4125 Equiv.

Part Number		Rail Length	Stroke	A	B	C	D	E	F	G	Load Rating (N/2 pcs.)	Unit Price	Volume Discount Rate
Type	No.												
SSRN36	12	304.8	228.6	-	152.4	254	-	149.2	260.3	273	481	1 ~ 3 pc(s).	4 ~ 20 pcs
	14	355.6	279.4	-	203.2	304.8	-	200	311.1	323.8	461		
	16	406.4	304.8	-	254	355.6	-	250.8	361.9	374.6	422		
	18	457.2	330.2	203.2	304.8	406.4	212.7	301.6	412.7	425.4	402		
	20	508	381	228.6	355.6	457.2	238.1	352.4	463.5	476.2	363		
	22	558.8	406.4	254	406.4	508	263.5	403.2	514.3	527	333		
	24	609.6	431.8	279.4	457.2	558.8	288.9	454	565.1	577.8	294		
	26	660.4	482.6	304.8	508	609.6	314.3	504.8	615.9	628.6	265		
	28	711.2	508	330.2	558.2	660.4	339.7	555.6	666.7	679.4	245		

For horizontal installation, the target value of load rating is 25% (Reference Value). The rails can not be pulled apart.
Use M4 Recessed Truss Machine Screws (P2-233, 234) or Recessed Binding Head Screws (P2-232) to mount rails.

Ordering Example

Part Number

SSRN3628

SR3624

Slide Rails

Medium Load, Steel, Stainless Steel

Load Rating: 294N~588N/2 pcs.


■Features: The rails are trivalent chrome coated steel. Economically priced slide rails compliant with RoHS regulations.

■Steel, Three-Step



RoHS10

SRX36



Rail Disassembly: **Not Possible**

Material: Steel

Surface Treatment: Bright Chromate (Trivalent Chromium)

Part Number		Rail Length	Stroke	A	B	C	D	Load Rating (N/2 pcs.)	Unit Price	Volume Discount Rate
Type	No.									
SRX36	12	305	324.2	-	149.2	260.3	273	500	1 ~ 5 pc(s).	6 ~ 20 pcs
	14	356	375.4	-	200	311.1	323.8	529		
	16	406	424.6	-	250.8	361.9	374.6	500		
	18	457	475.8	212.7	301.6	412.7	425.4	461		
	20	508	527	238.1	352.4	463.5	476.2	451		
	22	559	578.2	263.5	403.2	514.3	527	402		
	24	610	629.4	288.9	454	565.1	577.8	353		
	26	660	678.6	314.3	504.8	615.9	628.6	333		
	28	711	729.8	339.7	555.6	666.7	679.4	294		

For horizontal installation, the target value of load rating is 25% (Reference Value).
Three-step rail can be pulled out to the end. The rails can not be pulled apart.
Use M4 Recessed Truss Machine Screws (P2-233, 234) or Recessed Binding Head Screws (P2-232) to mount rails.


■Features: The rails are made of EN 1.4301 Equiv., which has excellent corrosion resistance.

■Stainless Steel, Three-Step



RoHS10

SSRX36



Rail Disassembly: **Not Possible**

Material: EN 1.4301 Equiv.

Ball: EN 1.4125 Equiv.

Part Number		Rail Length	Stroke	A	B	C	D	Load Rating (N/2 pcs.)	Unit Price	Volume Discount Rate
Type	No.									
SSRX36	12	304.8	327.2	-	149.2	260.3	273	588	1 ~ 5 pc(s).	6 ~ 20 pcs
	14	355.6	378	-	200	311.1	323.8	578		
	16	406.4	428.4	-	250.8	361.9	374.6	559		
	18	457.2	479.2	212.7	301.6	412.7	425.4	549		
	20	508.0	530	238.1	352.4	463.5	476.2	529		
	22	558.8	580.8	263.5	403.2	514.3	527	500		
	24	609.6	631.6	288.9	454	565.1	577.8	480		
	26	660.4	682.4	314.3	504.8	615.9	628.6	461		
	28	711.2	733.2	339.7	555.6	666.7	679.4	441		

For horizontal installation, the target value of load rating is 25% (Reference Value). Three-step rail can be pulled out to the end. The rails can not be pulled apart.
Use M4 Recessed Truss Machine Screws (P2-233, 234) or Recessed Binding Head Screws (P2-232) to mount rails.

Ordering Example

Part Number

SSRXN3620

SRX3624