

# Hollow Stands

## Set Screw Type

■ **Features:** Hollow Stands used as an equipment base for touch panel or box. Its Overall length can be specified freely.

■ **Set Screw**

RoHS10

Type		Material		Surface Treatment		Accessory	
Round Flanged	Compact Flanged	Hollow	Bracket	Trivalent Chromate	Electroless Nickel Plating	Black Oxide	Set Screw
Bracket 2 pcs./Bracket 1 pc.	Bracket 2 pcs./Bracket 1 pc.	EN 1.0480 Equiv.	EN 1.0038 Equiv.	-	-	-	-
PSEW	WPSEW	EN 1.0480 Equiv.	EN 1.0038 Equiv.	-	-	-	-
PSEK	WPSEK	EN 1.0480 Equiv.	EN 1.0038 Equiv.	-	-	-	-
PSEW	WPSEW	EN 1.4301 Equiv.	EN 1.4301 Equiv.	-	-	-	-

Set Bracket 2 pcs.

Bracket 1 pc.

Bracket only Round Flanged Bracket

Compact Flanged Bracket

Hollow Stand only

⚠ This product is offered as a set.  
L dimension tolerance is approx. ±2mm.  
⚠ Consider the Z3 Dimension when ordering only hollow tube for combined use with existing Stand-Up Bracket.

Part Number		Nominal	D	L	t	D1	D2	A	P.C.D.	T	H	l1	l2	M	l3	W	Z	W1							
Type				1mm Increment										(Coarse)											
Trivalent Chromate Electroless Nickel Plating Black Oxide	(Set)	30	30	200~800	4.0	30.5	42.7	90	70	10	50	15	M6	15	56	56	34								
	(Bracket only)	40	40	200~800		40.5	54.0	100	80		60	25							25	64	62	44			
		50	50.8	200~1000		51.5	65.0	110	90		75	30							30	74	74	50			
		60	60.5	200~1000		61.0	76.3	120	100		90	35							40	90	76	70			
Trivalent Chromate Electroless Nickel Plating Black Oxide		70	70	300~1000	6.0	70.5	89.1	130	110	12	105	45	M8	20	100	80	80								
		80	82.6	300~1000		83.5	101.6	140	120		120	40							60	110	86	90			
		100	101.6	350~1000		102.6	120.0	160	140		150	40							90	130	94	110			
		30	32	200~800		32.5	42.7	90	70		50	25							15						
Stainless Steel	(Set)	40	42.7	200~800	3.0	43.0	50.8	100	80	10	60	25	M6	15											
	Bracket 1 pc. Bracket 2 pcs.	50	50.8	200~1000		51.5	60.5	110	90		75	30							30						
		60	60.5	200~1000		61.0	76.3	120	100		90	35							40						
		70	76.3	300~1000		77.0	89.1	130	110		105	45							45						
	80	89.1	300~1000	90.0	101.6	140	120	120	40	60															
	100	101.6	350~1000	102.5	114.3	160	140	150	40	90															

Ordering Example: Part Number - L  
PSEW50 - 600  
PSEF100

■ **Bracket only**

Nominal	Unit Price			
	Round Flanged		Compact Flanged	
	Trivalent Chromate	Electroless Nickel Plating	Stainless Steel	Trivalent Chromate
30	PSEF	PSEFM	PSEFS	WPSEF
40				WPSEFM
50				
60				
70				
80				
100				

■ **Set**

Nominal	L	Unit Price									
		Round Flanged					Compact Flanged				
		Trivalent Chromate	Electroless Nickel Plating	Black Oxide	Stainless Steel	Trivalent Chromate	Electroless Nickel Plating	Black Oxide	Stainless Steel		
30	200~400										
	401~600										
	601~800										
40	200~400										
	401~600										
	601~800										
50	200~400										
	401~600										
	601~800										
60	200~400										
	401~600										
	601~800										
70	200~400										
	401~600										
	601~800										
80	200~400										
	401~600										
	601~800										
100	200~400										
	401~600										
	601~800										

■ **Hollow Stand only**

Nominal	L	Unit Price		
		Trivalent Chromate	Electroless Nickel Plating	Stainless Steel
30	200~400			
	401~600			
	601~800			
40	200~400			
	401~600			
	601~800			
50	200~400			
	401~600			
	601~800			
60	200~400			
	401~600			
	601~800			
70	200~400			
	401~600			
	601~800			
80	200~400			
	401~600			
	601~800			
100	200~400			
	401~600			
	601~800			

# Hollow Stands

## Welded Type

■ **Features:** Hollow Stands with accurate heights that can also be used as a spacer.

■ **Welded Type**

RoHS10

Type		Material		Surface Treatment	
Round Flanged	Compact Flanged	Hollow	Bracket	Trivalent Chromate	Electroless Nickel Plating
PSYM	WPSYM	EN 1.0480 Equiv.	EN 1.0038 Equiv.	-	-
PSYK	-	EN 1.0480 Equiv.	EN 1.0038 Equiv.	-	-

Round Flanged

Compact Flanged

Enlarged View: Only outside is welded.

Part Number		L	D	t	A	P.C.D.	T	W	Z	W1					
Type	Nominal	1mm Increment													
Round Flanged	30	50~300	30	4.0	90	70	10	56	56	34					
	40		±0.40								100	80	64	62	44
	50		±0.41								110	90	74	74	50
Compact Flanged	60		60.5	±0.49	6.0	120	100	12	90	76	70				
	70		70	±0.56		130	110		100	80	80				

Ordering Example: Part Number - L  
PSYM40 - 300

Nominal	L	Unit Price		
		Round Flanged		Compact Flanged
		Electroless Nickel Plating	Black Oxide	Electroless Nickel Plating
30	50~150	PSYM	PSYK	WPSYM
	151~300			
40	50~150			
	151~300			
50	50~150			
	151~300			
60	50~150			
	151~300			
70	50~150			
	151~300			

Alterations: Part Number - L - (LKC)  
PSYM40 - 300 - LKC

Alteration	Code	Spec.
	LKC	Changes the tolerance of L dimension to L±0.05. Ordering Code: LKC

