

Round Cords, Square Cords

Rubber, Rubber Sponge


■ Rubber-Sponge strings for various applications such as gap gasket.

Round Cords, Square Cords




Round Cords	Square Cords	Material	Hardness	Color
RBWN	RBKWN	Nitrile Rubber (NBR)	Shore A66	Black
RBWS	RBKWS	Silicon Rubber (SI)	Shore A50	Milky White
RBWF	-	Fluororubber (FPM)	Shore A69	Black
RBWCS	RBKWCS	Chloroprene Rubber Sponge	Asker C20	Black
RBWSS	RBKWSS	Silicon Rubber Sponge	Asker C25	Orange
RBWFS	-	Fluororubber Sponge	Asker C35	Black

Round Cords



Square Cords



Accuracy Standards

L Dimension Tolerance	Tolerance
200 or Less	±1.5
201~400	±2.0
401 or More	±3.5

Round Cords				Square Cords				Round Cords (Sponge Type)				Square Cords (Sponge Type)			
Part Number		1mm Increment	Selection (Meter)	Part Number		1mm Increment	Selection (Meter)	Part Number		L Selection (Meter)	Part Number		A Selection (Meter)		
Type	D	L		Type	A	L		Type	D		Type	A			
RBWN (Nitrile) RBWS (Silicon) RBWF (Fluorine)	2	20~999	1M 3M 5M 10M	RBKWN (Nitrile) RBKWS (Silicon)	5	20~999	1M 3M 5M 10M	RBWCS (Chloroprene Sponge) RBWSS (Silicon Sponge) RBWFS (Fluoro Sponge)	3	1M 3M 5M 10M	RBKWCS (Chloroprene Sponge) RBKWSS (Silicon Sponge)	5	1M 3M 5M 10M		
	3				6				4			6			
	4				7				5			7			
	5				8				6			8			
	6				9				7			9			
	7				10				8			10			
	8				12				9			12			
	9				15				10			15			

Ordering Example

Part Number - L

RBWN2 - 250

RBKWN15 - 1M

⚠ The price of this product is the unit price shown in the table multiplied by material multiplier.

(Ex.) Part Number - L >> (Unit Price) x (Material Multiplier) = Standard Type Unit Price

RBWS2 - 250

Part Number		D Dimension Tolerance	Unit Price									
Type	D		L									
			1mm Increment					Selection (Meter)				
			20~100	101~200	201~300	301~600	601~800	801~999	1M	3M	5M	10M
RBWN	(x1.0)	±0.35	2									
Nitrile			3									
RBWS	(x1.5)		4									
Silicon			5									
RBWF	(x1.0)	±0.5	6									
Fluorine			7									
D2~4;(x3.0)			8									
D5~8;(x5.0)			9									
D9~15;(x7.0)		±0.8	10									
() Material Multiplier			12									
		±1.0	15									

⚠ Material multiplier for RBWF may vary depending on D dimensions.

Part Number		A Dimension Tolerance	Unit Price									
Type	A		L									
			1mm Increment					Selection (Meter)				
			20~100	101~200	201~300	301~600	601~800	801~999	1M	3M	5M	10M
RBKWN	(x1.0)	±0.5	5									
Nitrile			6									
RBKWS	(x1.5)		8									
Silicon		±0.8	10									
() Material Multiplier			12									
		±1.0	15									

Part Number		D Dimension Tolerance	Unit Price			
Type	D		L Selection (Meter)			
			1M	3M	5M	10M
Round Cords		±1.0				
RBWCS	(x1.0)					
Chloroprene Sponge						
RBWSS	(x1.5)	±2.0				
Silicon Sponge						
() Material Multiplier						

⚠ Fluoro Sponge is selectable from D=5, 6, 8 or 10.

⚠ Fluoro Sponge Price has been revised due to the price list integration.

Part Number		A Dimension Tolerance	Unit Price			
Type	A		L Selection (Meter)			
			1M	3M	5M	10M
RBKWCS	(x1.0)	±1.0				
Chloroprene Sponge						
RBKWSS	(x1.5)					
Silicon Sponge		±2.0				
() Material Multiplier						
Part Number		D Dimension Tolerance	Unit Price			
Type	D		L Selection (Meter)			
			1M	3M	5M	10M
Round Cords		±1.0				
RBWFS						
Fluororubber Sponge						
		±2.0				

Round Dome Cords, Trapezoidal Dome Cords

Rubber, Rubber Sponge


■ Can be used for gaskets on door openings in order to enhance air-tightness or to prevent twists.

Round Dome Cords, Trapezoidal Dome Cords




Round Dome	Trapezoidal Dome	Material	Hardness	Color
KMHN	KYHN	Nitrile Rubber (NBR)	Shore A70	Black
KMHS	KYHS	Silicon Rubber (SI)		Red Brown
KMHF	KYHF	Fluororubber (FPM)	Asker C20	Black
KMHNS	-	Chloroprene Rubber Sponge		Black
KMHSS	-	Silicon Rubber Sponge	Asker C25	Orange

Round Dome



Trapezoidal Dome



Accuracy Standards

L Dimension Tolerance	Tolerance
200 or Less	±1.5
201~400	±2.0
401 or More	±3.5

Round Dome				Trapezoidal Dome				Round Dome (Sponge Type)			
Part Number		1mm Increment	L Selection (Meter)	Part Number		1mm Increment	L Selection (Meter)	Part Number			L Selection (Meter)
Type	A	L		Type	A	L		Type	A		
KMHN (Nitrile)	8	20~999	1M 3M 5M 10M	KYHN (Nitrile)	8	20~999	1M 3M 5M 10M	KMHNS (Chloroprene Sponge)	10	1M 3M 5M 10M	
KMHS (Silicon)	10			KYHS (Silicon)	10			KMHNS (Chloroprene Sponge)	15		
KMHF (Fluorine)	12			KYHF (Fluorine)	12			KMHSS (Silicon Sponge)	15A		
	15				16				20		
	16				20						

Part Number		A Dimension Tolerance	B	H	R	Unit Price							
Type	A					L							
						1mm Increment					Selection (Meter)		
						20~100	101~200	201~300	301~600	601~800	801~999	1M	3M
												5M	10M
KMHN	(x1.0)	±0.2	4	8	4								
Nitrile			5	10	5								
KMHS	(x1.5)		6	12	6								
Silicon			7.5	15	7.5								
KMHF	(x1.0)	±0.4	8	16	8								
Fluorine													
() Material Multiplier													

⚠ Material Multiplier for Fluororubber KMHF: When A=8, 10 or 12, (Unit Price x4.0). When A=15 or 16, (Unit Price x5.0).

Part Number		A Dimension Tolerance	B	H	R	Unit Price							
Type	A					L							
						1mm Increment					Selection (Meter)		
						20~100	101~200	201~300	301~600	601~800	801~999	1M	3M
												5M	10M
KYHN	(x1.0)	±0.2	4	8	2.8								
Nitrile			5	10	2.8								
KYHS	(x1.5)		6	12	3								
Silicon			8	16	4								
KYHF	(x1.0)	±0.4	10	20	5								
Fluorine													
() Material Multiplier													

⚠ Material Multiplier for Fluororubber KMHF: When A=8, 10 or 12, (Unit Price x4.0). When A=15 or 16, (Unit Price x5.0).

Part Number		A Dimension Tolerance	B	H	R	Unit Price			
Type	A					L Selection (Meter)			
						1M	3M	5M	10M
KMHNS	(x1.0)	±1.0	5	10	5				
Chloroprene Sponge			2.5	10	7.5				
KMHSS	(x1.5)		7.5	15	7.5				
Silicon Sponge			10	20	10				
() Material Multiplier									

⚠ The price of this product is the unit price shown in the table multiplied by material multiplier.

(Ex.) Part Number - L >> (Unit Price) x (Material Multiplier) = Standard Type Unit Price

KMHSS - 20

Ordering Example

Part Number - L

KMHN8 - 250

KMHNS15 - 10M