

Accessory Parts

RoHS10

Part Number	Material	Surface Treatment
JBS201	EN 1.4305 Equiv.	-
JBS301	EN 1.0330 Equiv.	Trivalent Chromate
FFS102	EN 1.0320 Equiv. (hot coiled)	Trivalent Chromate
JBS306	Polychloroprene	-
JBS402	Styrene-butadiene Rubber	-

Frame Jointing Fitting **JBS201**
Saddles with One Fixing **JBS301** (Set of 4)
Saddles with Two Fixings **FFS102** (Set of 4)
JBS306
Inner Rubber Cap **JBS402**
Outer Rubber Cap **JBS403**

Part Number	Mass (g)	Unit Price
JBS201	59	
JBS301	19	
FFS102	24	
JBS306	28	
JBS402	15	
JBS403	31	

* JBS301 and FFS102 is in set of 4 pieces.

RoHS10

Part Number	Material	Surface Treatment
JBS601	Polyester	-
JBS601S		
JBS611		
JBS612		
FFS106	EN 1.0038 Equiv.	Chrome Plating

Name Holder **JBS601**
Name Holder **JBS601S**
Name Holder **JBS611**
Name Holder **JBS612**
Ring Slider **FFS106** (Set of 10)

Part Number	Mass (g/pc.)	Unit Price
JBS601	34	
JBS601S	16	
JBS611	49	
JBS612	41	
FFS106	14	

ex Example

Adjusting Bolts

Part Number	Material	Surface Treatment
JBS202	EN 1.0330 Equiv.	Trivalent Chromate
JBS401	Polypropylene	-
JBS404	EN 1.0330 Equiv.	Trivalent Chromate
JBS405	EN 1.0330 Equiv.	Trivalent Chromate
JBS406	Plastic Styrene-butadiene Rubber	-
JBS407	AAS Resin	-

Adjuster **JBS401**
Adjusting Bolt A set **JBS404**
Adjusting Bolt B set **JBS405**
Insert Nut **JBS406**
Pipe Stand S **JBS202**
Inner Stand **JBS407**
Inner Stand **JBS408**

Stroke: 20mm
 Adjustment Range: 40mm
 Adjustment Range: 50mm

Part Number	Color	Mass (g)	Unit Price
JBS202	-	302	
JBS401	W, S	35	
JBS404	-	330	
JBS405	-	305	
JBS406	-	75	
JBS407	-	126	
JBS408	W (White)	92	

Ordering Example Part Number - Color
JBS202
JBS401 - W

Insert Nut - Stainless Steel

PFINS

Tapered part from tip to head (1.2°) allows insertion into the I.D. of pipe frames.

RoHS10 Material: Stainless Steel

Part Number	Mass (g)	Unit Price
PFINS	89	
	85	
	82	

Ordering Example Part Number
PFINS10

Can be used for Standard Leveling Mounts (P.1107).