



DIN Bushings

-DIN172A DIN179A-

CAD Data




RoHS10


Type		Material	D	Hardness
Shouldered	Straight			
DIN172A	DIN179A	1.0718/ 11SMnPb30	2.5-26	62 +/-2 HRC
		1.7131/ 16MnCr 5	28-35	

$6.3 \sqrt{\left(\frac{0.8}{\sqrt{G}} \right)}$

DIN 172 A



DIN 179 A



All specifications without any tolerance according:
JIS B 0405-1991-m (DIN ISO 2768-m)

Part Number	D	D Tolerance	L			d n6	H	R	T
			F7	Short	Medium	Long			
DIN172A DIN179A	2.5	+0.016	6	9		5	8	1	2
	3	+0.006				6	9		2.5
	3.3								
	3.5					7	10		
	4		8	12	16	8	11		
	4.2	+0.022						1.5	3
	4.5	+0.010				10	13		
	5					12	15		
	5.5					15	18		
	6		10	16	20	18	22		
	6.5					22	26	2	4
	6.8					26	30		
	7								
	7.5					30	34		
	8	+0.028				35	39		
	8.5	+0.013				42	46		
	9		12	20	25	48	52	3	5
	9.5								
	10								
	10.2								
	10.5								
	11								
	12								
	13	+0.034							
	14	+0.016							
	15		16	28	36				
	16								
	17								
	18								
	19								
	20								
	22		20	36	45				
	24	+0.041							
	25	+0.020							
	26								
	28								
	30		25	45	56				
	35	+0.050							
		+0.025							



Order
Example

Part Number - D - L
DIN179A - D5.5 - L10