

# BA 140806 F-7024



Bocube Alu  
Enclosure with membrane lid, graphite grey, covers anodised, hinged

Order no.: 00123124

**Colour of enclosure group**

Graphite grey, similar to RAL 7024; light grey, similar to RAL 7035; special colours on request


**Protection class**

IP 66 / IP 67 / IP 69 DIN EN 60529

**Enclosure material**

Enclosure: GD Al Si 12, seal PU foamed; Hinges / covers: Al Mg Si 0.5 powder-coated / natural-coloured anodised

Scope of delivery: enclosure incl. hinge and fixing material



<b>A</b>	159 mm
<b>B</b>	86 mm
<b>C</b>	60 mm
<b>a1</b>	113,5 mm
<b>a2</b>	115,5 mm
<b>b1</b>	72,5 mm
<b>b2</b>	77,5 mm
<b>c1</b>	51,5 mm

**Technical drawings**

Catalogue drawing in DXF format:  
[00123124\\_BA-140806-F-7024.dxf](#) (2.8 MB)

Catalogue drawing in PDF format:  
[00123124\\_BA-140806-F-7024.pdf](#) (222 KB)

3D product data in STEP format:

[Registration necessary](#)

Basic drawing for processing work:

[00123124\\_BA-140806-F-7024-G.dxf](#) (2.2 MB)

**Assembly instructions**

[Bocube Alu\\_00911501.pdf](#) (127 KB)

**Chapter download**

[Bocube Alu\\_GB.pdf](#) (1.7 MB)

\* = Available on request