

HUBER+SUHNER® DATA SHEET

Coaxial Panel Connector: 22_BNC-75-0-1/133_N

Rev.: B



Description

Straight bulkhead receptacle jack

Interface standards
IEC 60169-8_MIL-STD-348A/301_CECC 22120

Technical Data

Electrical Data

Impedance 75 Ω
Interface frequency max. 1 GHz

Mechanical Data

Weight 0.0108 kg

Environmental Data

Operating Temperature -65 °C to 165 °C
2002/95/EC (RoHS) compliant

Material Data

Piece Parts

Centre contact	Copper Beryllium Alloy
Outer contact	Brass
Body	Brass
Insulator	PFA / PTFE
Gasket	MVQ (Silicone Rubber)
Fastening nut	Brass
Washer	Bronze

Surface Plating

Gold Plating (Nickel underplated)
SUCOPLATE (R) Plating

Related Documents

Outline drawing DOU-00010476
Catalogue drawing DCA-00010478
Mounting hole DOU-00010411

Ordering Information

Single package 22_BNC-75-0-1/133_NE

HUBER+SUHNER is certified according to ISO 9001 and ISO 14001

WAIVER!

It is exclusively in written agreements that we provide our customers with warrants and representations as to the technical contained specifications and/or the fitness for any particular purpose. The facts and figures herein are carefully compiled to the best of our knowledge, but they are intended for general informational purposes only.



HUBER+SUHNER AG

RF Technology

9100 Herisau, Switzerland

Phone +41 (0)71 353 41 11

Fax +41 (0)71 353 45 90

www.hubersuhner.com

HUBER+SUHNER – Excellence in Connectivity Solutions