

## Coaxial Cable Connector 11\_UHF-0-7-17/033\_-

### Description

Straight cable plug

Interface standards  
IEC 60169-12



### Technical Data

#### Electrical Data

Impedance	other $\Omega$
Interface frequency max.	0.2 GHz

#### Mechanical Data

Centre contact	crimped
Outer contact	crimped
Weight	0.0238 kg

#### Environmental Data

Operating temperature	-55 °C to 165 °C
2011/65/EU (RoHS)	compliant

#### Material Data

Piece Parts	Material	Surface Plating
Centre contact	Brass	Silver Plating
Outer contact	Brass	SUCOPALATE (R) Plating
Body	Brass	SUCOPALATE (R) Plating
Insulator	PSU (Polysulfone)	
Coupling nut	Brass	SUCOPALATE (R) Plating
Crimp ferrule	Copper	

### Related Documents

Outline drawing	DOU-00181576
Catalogue drawing	DCA-00045040
Assembly instruction	DOC-0000201061

### Ordering Information

Single package 11\_UHF-0-7-17/033\_-E

### Additional Information

Suitable cables RG\_213\_/U, GX\_07272, G\_07262, G\_07272, RADOX\_RF\_213