

## Coaxial Cable Connector 16\_BNC-50-3-13/133\_N

### Description

Right angle cable plug

Interface standards

IEC 60169-8\_MIL-STD-348A/301\_CECC 22120



### Technical Data

#### Electrical Data

Impedance	50 Ω
Interface frequency max.	4 GHz

#### Mechanical Data

Centre contact	crimped
Outer 2contact	crimped
Weight	0.0261 kg

#### Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS)	compliant

#### Material Data

Piece Parts	Material	Surface Plating
Centre contact	Bronze / Brass	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	VMQ (Silicone rubber)	
Crimp ferrule	Copper	

### Related Documents

Outline drawing	DOU-00071565
Catalogue drawing	DOU-00006048
Assembly instruction	DOC-0000179061

### Ordering Information

Single package	16_BNC-50-3-13/133_NE
----------------	-----------------------

### Additional Information

Suitable cables	RG_58_C/U, G_03232, GX_03272
-----------------	------------------------------