

Coaxial Cable Connector 24_BNC-50-2-20/133_N

Description

Straight bulkhead cable feed through

Interface standards

IEC 60169-8_MIL-STD-348A/301_CECC 22120



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	4 GHz

Mechanical Data

Centre contact	soldered
Outer contact	soldered
Weight	0.0153 kg

Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Gasket	VMQ (Silicone rubber)	
Fastening nut	Brass	
Washer	Bronze	

Related Documents

Outline drawing	DOU-00009309
Catalogue drawing	DCA-00009310
Assembly instruction	DOC-0000179119
Mounting hole	DOU-00008751

Ordering Information

Single package	24_BNC-50-2-20/133_NE
----------------	-----------------------

Additional Information

Suitable cables	EZ_86_TP_M17
-----------------	--------------