

Coaxial Panel Connector 23_SHV-50-0-2/133_N

Description

Straight panel receptacle jack, flange mount

Interface standards

IEC 60498_MIL-STD-348A/314



Technical Data

Electrical Data

Impedance 50 Ω
Interface frequency max. 0.3 GHz

Mechanical Data

Number of matings 500
Weight 0.0143 kg

Environmental Data

Operating temperature -65 °C to 165 °C
2011/65/EU (RoHS) compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Brass	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	

Related Documents

Outline drawing DOU-00068553
Catalogue drawing DCA-00011171
Mounting hole DOU-00010585

Ordering Information

Single package 23_SHV-50-0-2/133_NE